

RoHS

REV.

ECN.#

DESCRIPTION

NAME




DATE

A0



NEW RELEASE

liuhongping

2023.01.02



PIN NO.	DIM. A	DIM. B	DIM. C
06	7.40	2.50	3.57
08	8.40	3.50	4.57
10	9.40	4.50	5.57
12	10.40	5.50	6.57
14	11.40	6.50	7.57
16	12.40	7.50	8.57
18	13.40	8.50	9.57
20	14.40	9.50	10.57
22	15.40	10.50	11.57
24	16.40	11.50	12.57
26	17.40	12.50	13.57
28	18.40	13.50	14.57
30	19.40	14.50	15.57
32	20.40	15.50	16.57
34	21.40	16.50	17.57
36	22.40	17.50	18.57
40	24.40	19.50	20.57
45	26.90	22.00	23.07
50	29.40	24.50	25.57




技术指标:

1. 胶芯: LCP UL94V-0 本色
2. 掀盖: LCP UL94V-0 黑色
3. 端子: 磷青铜/表面镀锡
4. 焊片: 黄铜/表面镀锡
5. 温度范围: $-30^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
6. 额定电流: 0.5A.
7. 额定电压: 25V, AC/DC(等效).
8. 接触电阻: $\leq 40\text{m}\Omega$.
9. 绝缘电阻: $\geq 50\text{M}\Omega$.
10. 耐电压: 200V AC.
11. 端子接触区盐雾: 8小时.

料号:

111510572-XX

PIN NO. (CKT)



RECOMMENDED FPC/FFC DIMENSION


MILLIMETERS	INCH
X* $\pm 2^{\circ}$	X* $\pm 2^{\circ}$
X ± 0.30	.X ± 0.012
XX ± 0.20	.XX ± 0.008
XXX ± 0.10	.XXX ± 0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd.	

东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	FPC 0.5间距 2.0H掀盖下接	DR	
PART NO.	111510572-XX	CHKD	
PRO J.	PAGE 1/5 UNITS mm	APPD	
SIZE	A4 SCALE 1:1 DIS NO.		

RECOMMEND PCB LAYOUT
TOLERANCE: ± 0.05

RoHS




COVER TAPE PEELING ANGLE: 165°~180°
PEELING FORCE: 20~130g

CARRIER TAPE


USER DIRECTION OF UNREELING

DETAIL B




NOTES

1. NUMBER OF CONNECTORS: 2000PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 34 000PCS/CARTON




适应料号: 06P~10P

111510572-06 到 111510572-10

MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD				
X* ±2"	X* ±2"					
X ±0.30	.X ±0.012	TITLE FPC 0.5间距 2.0H掀盖下接 DR				
XX ±0.20	.XX ±0.008	PART NO. 111510572-XX CHKD				
XXX ±0.10	.XXX ±0.004	PRO J. PAGE 2/5 UNITS mm APPD				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		SIZE A4 SCALE 1:1 DIS NO.				

RoHS




COVER TAPE PEELING ANGLE: 165°~180°
PEELING FORCE: 20~130g

CARRIER TAPE


USER DIRECTION OF UNREELING

DETAIL B




NOTES

1. NUMBER OF CONNECTORS: 2000PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 24 000PCS/CARTON




适应料号: 12P~24P

111510572-12 到 111510572-24

MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD				
X* ±2"	X* ±2"					
X ±0.30	.X ±0.012	TITLE FPC 0.5间距 2.0H掀盖下接 DR				
XX ±0.20	.XX ±0.008	PART NO. 111510572-XX CHKD				
XXX ±0.10	.XXX ±0.004	PRO J. PAGE 3/5 UNITS mm APPD				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		SIZE A4 SCALE 1:1 DIS NO.				

RoHS




COVER TAPE PEELING ANGLE: 165°~180°
PEELING FORCE: 20~130g

CARRIER TAPE


USER DIRECTION OF UNREELING

DETAIL B




NOTES

1. NUMBER OF CONNECTORS: 2000PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 20 000PCS/CARTON




适应料号: 26P~32P

111510572-26 到 111510572-32

MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD				
X* ±2"	X* ±2"					
X ±0.30	.X ±0.012	TITLE FPC 0.5间距 2.0H掀盖下接 DR				
XX ±0.20	.XX ±0.008	PART NO. 111510572-XX CHKD				
XXX ±0.10	.XXX ±0.004	PRO J. PAGE 4/5 UNITS mm APPD				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		SIZE A4 SCALE 1:1 DIS NO.				

RoHS


USER DIRECTION OF UNREELING

COVER TAPE PEELING ANGLE: $165^\circ \sim 180^\circ$ PEELING FORCE: $20 \sim 130g$

CARRIER TAPE


USER DIRECTION OF UNREELING

DETAIL B




NOTES

1. NUMBER OF CONNECTORS: 2000PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 14 000PCS/CARTON

CARTON
350*350*375

适应料号: 36P~50P

111510572-36 到 111310542-50

MILLIMETERS	INCH
X* $\pm 2^*$	X* $\pm 2^*$
X ± 0.30	.X ± 0.012
XX ± 0.20	.XX ± 0.008
XXX ± 0.10	.XXX ± 0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	

东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	FPC 0.5间距 2.0H掀盖下接	DR		
PART NO.	111510572-XX	CHKD		
PRO J.	PAGE 5/5	UNITS mm	APPD	
SIZE	A4	SCALE 1:1	DIS NO.	