




RoHS





REV.	ECN.#	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	HZP	2023.01.02



Section A-A
Scale 2:1



FPC/FFC Insert Direction
Recommended P.C.B Layout



Recommended FPC Dimension

Note:

1.Material

- 1.1: Housing: LCP UL94-V0 Color:Nature.
1.2: Actuator: LCP UL94-V0 Color:Black.
1.3: Contact: Phosphor Bronze.
1.4: LEG: Brass.

2.Plating

- 2.1: Contact:Gold Plating Nickel Overall .
2.2: LEG: Matte Tin Plating Over Nickel.

3.Rating:

- 3.1: Operating Voltage: 50V AC/DC.
3.2: Current Rating: 0.4A AC/DC.
3.3: Operating Temperature:-25°C~+85°C.

PIN	A	B	C	D	PIN	A	B	C	D
41	24.90	20.00	24.50	21.00	42	25.40	20.50	25.00	21.50
4	6.40	1.50	6.00	2.50	43	25.90	21.00	25.50	22.00
5	6.90	2.00	6.50	3.00	44	26.40	21.50	26.00	22.50
6	7.40	2.50	7.00	3.50	45	26.90	22.00	26.50	23.00
7	7.90	3.00	7.50	4.00	46	27.40	22.50	27.00	23.50
8	8.40	3.50	8.00	4.50	47	27.90	23.00	27.50	24.00
9	8.90	4.00	8.50	5.00	48	28.40	23.50	28.00	24.50
10	9.40	4.50	9.00	5.50	49	28.90	24.00	28.50	25.00
11	9.90	5.00	9.50	6.00	50	29.40	24.50	29.00	25.50
12	10.40	5.50	10.00	6.50	51	29.90	25.00	29.50	26.00
13	10.90	6.00	10.50	7.00	52	30.40	25.50	30.00	26.50
14	11.40	6.50	11.00	7.50	53	30.90	26.00	30.50	27.00
15	11.90	7.00	11.50	8.00	54	31.40	26.50	31.00	27.50
16	12.40	7.50	12.00	8.50	55	31.90	27.00	31.50	28.00
17	12.90	8.00	12.50	9.00	56	32.40	27.50	32.00	28.50
18	13.40	8.50	13.00	9.50	57	32.90	28.00	32.50	29.00
19	13.90	9.00	13.50	10.00	58	33.40	28.50	33.00	29.50
20	14.40	9.50	14.00	10.50	59	33.90	29.00	33.50	30.00
21	14.90	10.00	14.50	11.00	60	34.40	29.50	34.00	30.50
22	15.40	10.50	15.00	11.50	61	34.90	30.00	34.50	31.00
23	15.90	11.00	15.50	12.00	62	35.40	30.50	35.00	31.50
24	16.40	11.50	16.00	12.50	63	35.90	31.00	35.50	32.00
25	16.90	12.00	16.50	13.00	64	36.40	31.50	36.00	32.50
26	17.40	12.50	17.00	13.50	65	36.90	32.00	36.50	33.00
27	17.90	13.00	17.50	14.00	66	37.40	32.50	37.00	33.50
28	18.40	13.50	18.00	14.50	67	37.90	33.00	37.50	34.00
29	18.90	14.00	18.50	15.00	68	38.40	33.50	38.00	34.50
30	19.40	14.50	19.00	15.50	69	38.90	34.00	38.50	35.00
31	19.90	15.00	19.50	16.00	70	39.40	34.50	39.00	35.50
32	20.40	15.50	20.00	16.50	71	39.90	35.00	39.50	36.00
33	20.90	16.00	20.50	17.00	72	40.40	35.50	40.00	36.50
34	21.40	16.50	21.00	17.50	73	40.90	36.00	40.50	37.00
35	21.90	17.00	21.50	18.00	74	41.40	36.50	41.00	37.50
36	22.40	17.50	22.00	18.50	75	41.90	37.00	41.50	38.00
36	22.40	17.50	22.00	18.50	76	42.40	37.50	42.00	38.50
37	22.90	18.00	22.50	19.00	77	42.90	38.00	42.50	39.00
38	23.40	18.50	23.00	19.50	78	43.40	38.50	43.00	39.50
39	23.90	19.00	23.50	20.00	79	43.90	39.00	43.50	40.00
40	24.40	19.50	24.00	20.50	80	44.40	39.50	44.00	40.50

MILLIMETERS	INCH
X.* ±2"	X.* ±2"
X ±0.30	.X ±0.012
XX ±0.20	.XX ±0.008
XXX ±0.10	.XXX ±0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBilal Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBilal Metal Plastic Technology Co.,Ltd	



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	FPC 0.5间距 2.0H 掀盖下接 (镀金)	DR		
PART NO.	111310572-XX	CHKD		
PRO J.	PAGE 1/1 UNITS mm	APPD		
SIZE	A4 SCALE 1:1 DIS NO.			