

RoHS

REV.

ECN.#

DESCRIPTION

NAME




DATE

A0

NEW RELEASE

HZP

2023.01.02



Note:

1.Material

- 1.1: Housing: LCP UL94-V0 Color:Black/Natural
1.2: Actuator: LCP OR PA UL94-V0 Color:Black.
1.3: Contact: Phosphor Bronze.
1.4: LEG: Phosphor Bronze.



2.Plating

- 2.1: Contact: G/F Plating Over Nickel..
2.2: LEG: Matte Tin Plating Over Nickel.


3.Rating:

- 3.1: Operating Voltage: 30V AC/DC.
3.2: Current Rating: 0.2A AC/DC.
3.3: Operating Temperature:-55~C~+85~C.

No1 Contact Point




No2 Contact Point



FPC/FFC Insert Direction
Recommended P.C.B Layout

Number of Contacts	Dimension				
	A	B	C	D	E
11	4.80	2.40	3.00	3.63	4.30
13	5.40	3.00	3.60	4.23	4.90
15	6.00	3.60	4.20	4.83	5.50
17	6.60	4.20	4.80	5.43	6.10
19	7.20	4.80	5.40	6.03	6.70
21	7.80	5.40	6.00	6.63	7.30
23	8.40	6.00	6.60	7.23	7.90
25	9.00	6.60	7.20	7.83	8.50
27	9.60	7.20	7.80	8.43	9.10
29	10.20	7.80	8.40	9.03	9.70
31	10.80	8.40	9.00	9.63	10.30
33	11.40	9.00	9.60	10.23	10.90
35	12.00	9.60	10.20	10.83	11.50
37	12.60	10.20	10.80	11.43	12.10
39	13.20	10.80	11.40	12.03	12.70
41	13.80	11.40	12.00	12.63	13.30
45	15.00	12.60	13.20	13.83	14.50
49	16.20	13.80	14.40	15.03	15.70
51	16.80	14.40	15.00	15.63	16.30



Applicable FPC

MILLIMETERS	INCH
X' ±2'	X' ±2'
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBilai Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBilai Metal Plastic Technology Co.,Ltd



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	FPC 0.3PITCH 1.0H 前掀	DR		
PART NO.	111310522-XX	CHKD		
PRO J.	PAGE 1/2	UNITS mm	APPD	
SIZE	A4	SCALE 1:1	DIS NO.	