

RoHS

REV.

ECN.#

DESCRIPTION

NAME


DATE

A0

NEW RELEASE

HZP

2023.01.02









1. MATERIAL:

HOUSING: LCP (UL94-V0), COLOR: NATURAL.
CONTACTS: COPPER ALLOY. G/F OVER 30u" Ni.
PEG: COPPER ALLOY.Sn 60u" MIN.Ni 30u" MIN
ACTUATOR: LCP (UL94-V0). COLOR:BLACK

2. RATING:

OPERATING VOLTAGE: 50Vrms AC.
CURRENT RATING: 0.5A.
OPERATING TEMPERATURE: -55°C~+85°C.
OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)
STORAGE TEMPERATURE RANGE: -10°C~+50°C.
STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)



Long cover type

MILLIMETERS	INCH
X.* ±2*	X.* ±2*
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF DongGuan JinBiLai
Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE
PRIOR WRITTEN CONSENT OF DongGuan
JinBiLai Metal Plastic Technology Co.,Ltd




东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	0.5Pitch 1.0H ZIF 前插后 掀式	DR		
PART NO.	111310512-XX	CHKD		
PRO J.	PAGE 1/2 UNITS mm	APPD		
SIZE	A4 SCALE 1:1 DIS NO.			

Technical drawing of a mechanical part with dimensions:

- Overall width: 3.30
- Top edge dimensions: 0.80 ± 0.05 , 0.40 ± 0.05
- Central section width: 0.50
- Right edge dimensions: 0.30 ± 0.03 , (0.25)
- Left side features: 0.80 , 0.35 , 0.15
- Bottom edge dimensions: (0.15) , (0.15) , (2.90)
- Overall length: $D \pm 0.05$
- Central section length: B

Recommended metal mask thickness: $t=0.1$ 

<i>Number of Contacts</i>	<i>DIM A</i>	<i>DIM B</i>	<i>DIM C</i>	<i>DIM D</i>	<i>DIM E</i>
50	27.00	24.50	25.57	26.39	25.50
45	24.50	22.00	23.07	23.89	23.00
40	22.00	19.50	20.57	21.39	20.50
36	20.00	17.50	18.57	19.39	18.50
34	19.00	16.50	17.57	18.39	17.50
32	18.00	15.50	16.57	17.39	16.50
30	17.00	14.50	15.57	16.39	15.50
28	16.00	13.50	14.57	15.39	14.50
26	15.00	12.50	13.57	14.39	13.50
24	14.00	11.50	12.57	13.39	12.50
22	13.00	10.50	11.57	12.39	11.50
20	12.00	9.50	10.57	11.39	10.50
18	11.00	8.50	9.57	10.39	9.50
16	10.00	7.50	8.57	9.39	8.50
15	9.50	7.00	8.07	8.89	8.00
14	9.00	6.50	7.57	8.39	7.50
13	8.50	6.00	7.07	7.89	7.00
12	8.00	5.50	6.57	7.39	6.50
11	7.50	5.00	6.07	6.89	6.00
10	7.00	4.50	5.57	6.39	5.50
9	6.5	4.00	5.07	5.89	5.00
8	6.00	3.50	4.57	5.39	4.50
7	5.5	3.00	4.07	4.89	4.00
6	5.00	2.50	3.57	4.39	3.50
5	4.5	2.00	3.07	3.89	3.00
4	4.00	1.50	2.57	3.39	2.50

Long cover type

MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD									
X.* ±2°	X.* ±2°										
X ±0.30	.X ±0.012										
XX ±0.20	.XX ±0.008										
XXX ±0.10	.XXX ±0.004										
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Dongguan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF Dongguan JinBiLai Metal Plastic Technology Co.,Ltd		TITLE	0.5Pitch 1.0H ZIF 前插后 掀式				DR				
		PART NO.	111310512-XX				CHKD				
		PRO J.	PAGE	2/2	UNITS	mm	APPD				
			SIZE	A4	SCALE	1:1	DIS NO.				