








APPLICABLE P.C.B. DIMENSION

NOTES: MATERIAL&FINISH

1. HOUSING: HIGH THERMOPLASTIC; COLOR: BEIGE
2. TERMINAL: COPPER ALLOY. $t=0.15\text{mm}$
PLATING: CONTACT AREA GOLD $3\mu\text{Min.}$
SOLDER AREA MATTE TIN (LEAD FREE) $75\mu\text{Min.}$,
OVERALL WITH $50\sim 150\mu\text{NICKEL}$ UNDER PLATED.
3. SHELL: STAINLESS STEEL $t=0.15\text{mm}$
PLATING: SOLDER AREA PLATED WITH GOLD FLASH,
 $10\mu\sim 80\mu\text{NICKEL}$ UNDER PLATED
4. SPECIFICATIONS:
 - 4.1 CURRENT RATING: 1A AC, DC
 - 4.2 VOLTAGE RATING: 200V AC, DC
 - 4.3 WITHSTANDING VOLTAGE: 500V AC/MINUTE.
 - 4.4 INSULATION RESISTANCE: $100\text{M}\Omega\text{ MIN.}$
 - 4.5 CONTACT RESISTANCE: $40\text{m}\Omega\text{ MAX.}$
 - 4.6 OPERATING TEMPERATURE: $-40^{\circ}\text{C}\sim +80^{\circ}\text{C}$



CUSTOMER DRAWING			深圳市文章济美科技有限公司		
Tolerance Unspecified (未注公差)	Size (图幅): A4	Unit (单位): MM	Product Name (产品名称): LVDS 1.0 PITCH 30P H=2.3 CONN.		
0.0 ± 0.35 0° $\pm 5^{\circ}$ 0.00 ± 0.25 0° 0 $\pm 3^{\circ}$ 0.000 ± 0.15 0° 00 $\pm 1^{\circ}$	Scale (比例): 1:1	Page (页数): 1 OF 1	Product No (产品料号): 5001-LVDS123-**R1-00-B		
Project View (投影视角)	Rev (版本): A	Designer (设计): Chu 07/07/04	Checked (审核):	Approved (核准):	

Rev 版本	Change Description 变更内容	Date 日期	Revisor 制/修订人
A	初版发行	2017/07/04	Chu