








A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

料号编码:



RECOMMENDED P.C.B. LAYOUT (T:1.00mm)
TOLERANCE UNSPECIFIED ±0.05mm

Part Number		Product Description				
WTT-02F16BV835CG08		TYPE-C 16PIN four-legged board-mounted female socket L=8.35MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.30 X.X ± 0.20 X.XX ± 0.15 X.XXX ± 0.05	Units: Metric (mm)  3rd Angle Projection	 COMPLIANT ©2017 UL LLC UL94V-0	 RoHS COMPLIANT 2011/05/EU Deca-BDE	 REACH COMPLIANT 2011/05/EU SVHC
CHECKED	Xiong fangyuan					
APPROVED	Huangshaohuang					
Drawing Date	22/05/24					

WTT®

用心连接世界

SCALE 1:1 SIZE: A4 SHEET: 1 or 1