


REV.	10	11	12	13	14	15	16
ECR#							
DESCRIPTION							
DATE							
DRAWN							
CHECKED							
APPROVED							

NOTE:

- 1.Contact Resistance:40mOHM Max.;
- 2.Dielectric Withstanding Voltage:100V AC For 1 Minute;
- 3.Insulation Resistance:100M OHM Min.;
- 4.Mating And Unmating Force: Mating Force: 5~20N Unmating Force: 8~20N; 6~20N AFTER TEST;
- 5.Durability:10000 Cycles;




USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	SSTXp1	B11	SSRXp1
A3	SSTXn1	B10	SSRXn1
A4	Vbus	B9	Vbus
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	Vbus	B4	Vbus
A10	SSRXn2	B3	SSTXn2
A11	SSRXp2	B2	SSTXp2
A12	GND	B1	GND






CAP示意图 SC: 1:2

Item	Title	Material	Dispose	Q'TY
1	Shell	SUS304	Ni:30u" Min.	1PCS
2	GND Plate	SUS301		2PCS
3	Mid Plate	SUS301		1PCS
4	Contact	C7025	Mating Area: Gold Solder Tails: Matt Tin	2PCS
5	InsertMolding	LCP E6808	UL 94V-0 Black	1PCS
6	COVER	LCP E6808	UL 94V-0 Black	1PCS



RECOMMEND P. C. B LAYOUT (COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ± 0.05



料号编码:

WTT - XX X X X XXX XX XX

公司品牌 内部编码 产品流水号


产品系列 CG:常规系列
FS:防水系列
DT:外壳带弹片系列
WZ:无柱系列

产品高度 120:12.0H
130:13.0H
135:13.5H
150:15.0H
以此类推

上板类型 A:立式 C:沉板 J:夹板 V:插贴 H:焊线

产品结构 D:插件 B:卧式 C:侧立式

PIN 数 06:6P 16:16P 24:24P 以此类推

Part Number		Product Description				
WTT-02F24AV120CG21		TYPE-C 24PIN Vertical SMD H12.0MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.30 X.X ± 0.20 X.XX ± 0.15 X.XXX ± 0.05	Units: Metric (mm)			
CHECKED	Xiong fangyuan		 3rd Angle Projection			
APPROVED	Huangshaohuang					
Drawing Date	22/05/24					

WTT®

用心连接世界

SCALE 1:1 SIZE: A4 SHEET: 1 or 1