









RoHS



- SPECIFICATIONS
- 1.Voltage rating: 50V AC, DC
 2. Current rating: 2A AC, DC
 3. Temperature range: -25°C ~ +85°C
 4. Insulation resistance: 100MΩ Min.
 5. Withstanding voltage: 500V AC/ minute.
 6. Contact resistance: 20mΩ Max.

Material:

Insulator Material:PA66 UL 94V-0

Accepts :T1201 terminal

Mate with:M1201 series heade

Ordering Code:

P1201-XX-BK

1 2

1.序列号

2.Pin位数:2-15P

No. of Pins/Row	Dimension				
	A	B	C	D	E
02	1.20	3.10	2.60	0.60	3.70
03	2.40	4.30	3.80	1.20	4.80
04	3.60	5.50	5.00	0.60	6.10
05	4.80	6.70	6.20	1.20	7.30
06	6.00	7.90	7.40	0.60	8.50
07	7.20	9.10	8.60	1.20	9.70
08	8.40	10.30	9.80	0.60	10.90
09	9.60	11.50	11.00	1.20	12.10
10	10.80	12.70	12.20	0.60	13.30
11	12.00	13.90	13.40	1.20	14.50
12	13.20	15.10	14.60	0.60	15.70
13	14.40	16.30	15.80	1.20	16.90
14	15.60	17.50	17.00	0.60	18.10
15	16.80	18.70	18.20	1.20	19.30

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN	

PART NO:		P1201-XX-BK		XFCN 兴飞连接器	
TITLE:		1.20mm Crimp Style Connectors			
				0769-82001899	
				www.xfconn.com	
				DWG NO: /	
APPD		Chen ZhiQiang			
CHKD		Liu Wei		VIEW	
DRAW		Chen HongJiang		SCALE	
DATE		2026.07.31		NONE	
				SHEET	
				1/1	
				REV	
				A1	