





备注:


- 1.材质:
 - 1.1 胶芯: LCP+30%G.F UL94V-0
 - 1.2 端子: 高导铜C7025, T=0.15mm;
 - 1.3 外壳: SUS304, T=0.30mm;
 - 1.4 中夹片: SUS301, T=0.15mm;
- 2.主要特性:
 - 2.1额定电压: 20V
 - 2.2额定电流: 5A
 - 2.3接触阻抗: 40mΩ MAX(初始值)
50mΩ MAX(测试后)
 - 2.4绝缘阻抗: 100MΩ MIN
 - 2.5耐压测试: 100V AC R.M.S.
 - 2.6整体插入力: 5-20N 整体插入力: 5-20N (耐久后)
整体拔出力:8-20N 整体拔出力:6-20N (耐久后)
 - 2.7耐久: 10000次
 - 2.8耐高温: 建议1. 波峰焊 2. SMT回流焊 (峰值 $260^{\circ}\pm 5^{\circ}$),
塑胶不能有起泡, 融胶等不良, 变色, 翘曲变形在公差范围以内;
 - 2.9产品须做焊锡测试, 粘锡面积达到95%以上;
 - 3.0盐雾测试: 48H
 - 3.1工作温度: $-30^{\circ}\text{C}\sim +85^{\circ}\text{C}$



料号编码: 装吸取盖示意图 12-0.25

Part Number		Product Description				
WTT-04F16AD131CG64		TYPE-C 16PIN upright plug-in board without spring plate H13.1MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. $\pm$ 0.40 X.X $\pm$ 0.30 X.XX $\pm$ 0.20 X.XXX $\pm$ 0.10	Units:			
CHECKED	Xiong fangyuan		Metric (mm)			
APPROVED	Huangshaohuang		 3rd Angle Projection			
Drawing Date	22/05/24					


REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED



- 备注:
- 1.把上下载带送入载带机进行调整,然后将产品按照指定的方式摆入下载带中,开动卷带机进行卷装(每卷包350PCS),
 - 2.在卷装OK的每卷盘面的指定位置上贴上物料标签装入纸箱内;每箱装10盘(3.5K/箱)
 - 3.纸箱用封箱带将其封好,胶带要求工字型,不可遮住标签;
 - 4.如果客户对包装标签另有要求,请按客户要求作业;有未满足之零数箱需用缓冲材料填充;
 - 5.上载带剥离力:0.2-1.2N.;

TABLE :

规格H	PCS/载带	K/箱
11.50	350PCS	3.5K
12.40	350PCS	3.5K
13.10	350PCS	3.5K

Part Number		Product Description				
WTT-04F16AD131CG64		TYPE-C 16PIN upright plug-in board without spring plate H13.1MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.40 X.X ± 0.30 X.XX ± 0.20 X.XXX ± 0.10	Units: Metric (mm)	 COMPLIANT 2012 UL LLC UL94V-0	 RoHS COMPLIANT 2011/05/EU Deca-BDE	 REACH COMPLIANT 2002/61/EC SVHC
CHECKED	Xiong fangyuan					
APPROVED	Huangshaohuang					
Drawing Date	22/05/24					
			 3rd Angle Projection			



用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 2 or 2
--------------	-------------	------------------