






技术要求:

1. 电气及机械特性要求如下:

- 1.1 接触阻抗: 50mΩ以下;
- 1.2 绝缘阻抗: 100MΩ以上;
- 1.3 耐电压: 500V AC以上;
- 1.4 耐插拔: 5,000次以上;
- 1.5 插入力: 0.3~3.0kgf (3~30N);
- 1.6 拔出力: 0.3~3.0kgf (3~30N).

2. 产品符合RoHS环保标准要求.

这两组开关脚
焊盘需外扩,
不能靠近塑胶
内部, 会进松
香的风险

RECOMMENDED PCB LAYOUT
TOP VIEW TOL:±0.05

(Ø3.50mm 4 POLE PLUG DETAIL DRAWING)

09	HOUSING	1 PCS	HIGH TEMPERATURE PLASTIC	BLACK COLOR
08	CONTACT G	1 PCS	BRASS T=0.20	Au Plated
07	CONTACT G	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
06	CONTACT F	1 PCS	BRASS T=0.20	Au Plated
05	CONTACT E	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
04	CONTACT D	1 PCS	BRASS T=0.20	Au Plated
03	CONTACT C	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
02	CONTACT B	1 PCS	BRASS T=0.20	Au Plated
01	CONTACT A	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
ITEM	PART NAME	Q'TY	MATERIAL	DESCRIPTION



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X" ±0.5" UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: PJ-393B 8P 全贴5.0头	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW-PJ393B8P-500B
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2609211437
			SHEET NO.	1 OF 1