






3D VIEW



SCHEMATIC



(ø3.50mm 4 POLE PLUG DETAIL DRAWING)

NOTES:

1. CONTACT CURRENT RATING:1A;
2. CONTACT RESISTANCE:50mΩ MAX;
3. INSULATION RESISTANCE:100MΩ MIN;
4. DIELECTRIC WITHSTANDING:500V AC MIN;
5. DURABILITY:5000CYCLES MIN;
6. CONNECTOR MATING FORCES:2.94~29.4N(0.3~3.0kgf);
7. CONNECTOR UNMATING FORCES:2.94~29.4N(0.3~3.0kgf);

05	CONTACT 5#	1 PCS	STAINLESS STEEL, T=0.20	Matte Tin
04	CONTACT 4#	1 PCS	PHOSPHOR BRONZE, T=0.20	Matte Tin
03	CONTACT 3#	1 PCS	PHOSPHOR BRONZE, T=0.20	Matte Tin
02	CONTACT 1#2#	1 PCS	PHOSPHOR BRONZE, T=0.20	Matte Tin
01	HOUSING	1 PCS	HIGH TEMPERATURE PLASTIC	BLACK,
ITEM	PART NAME	Q'TY	MATERIAL	DESCRIPTION



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5' UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: PJ-327F 全贴	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW02-PJ327F-500B
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2609211147
			SHEET NO.	1 OF 1