

REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED

备注:

1.材质:

1.1 胶芯: LCP+30%G.F UL94V-0

1.2 端子: 高导铜C7025,

1.3 外壳: SUS304,

1.4 中夹片: SUS301,

2.主要特性:

2.1额定电流: 5A

2.2接触阻抗: 40m Ω E MAX(初始值)

50m Ω MAX(测试后)

2.3绝缘阻抗: 100M Ω E MIN

2.4耐压测试: 100V AC R.M.S.

2.6整体插入力: 5-20N 整体插入力: 5-20N (耐久后)

整体拔出力:8-20N 整体拔出力:5-20N (耐久后)

2.7耐久: 10000次







2.8耐高温: SMT 回流焊 (峰值260 $\pm$ 5 $^{\circ}$), 塑胶不能有起泡,

融胶等不良,变色,翘曲变形在公差范围以内;

2.9产品须做焊锡测试,粘锡面积达到95%以上;

3.0盐雾测试: 48H MIN


3.1工作温度: -30 $^{\circ}$ C ~ +85 $^{\circ}$ C



PIN NUMBER	SIGNAL NAME
A1	GND
A2	SSTXp1
A3	SSTXn1
A4	VBUS
A5	CC1
A6	Dp1
A7	Dn1
A8	SBU1
A9	VBUS
A10	SSRXn2
A11	SSRXp2
A12	GND

PIN NUMBER	SIGNAL NAME
B12	GND
B11	SSRXp1
B10	SSRXn1
B9	VBUS
B8	SBU2
B7	Dn2
B6	Dp2
B5	CC2
B4	VBUS
B3	SSTXn2
B2	SSTXp2
B1	GND

料号编码:



Part Number		Product Description				
WTT-04F24BV900CG44		TYPE-C 24PIN Single Row Surface Mount on Board L=9.0MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.40 X.X ± 0.30 X.XX ± 0.20 X.XXX ± 0.10	Units: Metric (mm)	 COMPLIANT @2017 UL LLC UL94V-0	 RoHS COMPLIANT 2011/05/EU Deca-BDE	 REACH COMPLIANT 2011/05/EU SVHC
CHECKED	Xiong fangyuan		 3rd Angle Projection			
APPROVED	Huangshaohuang					
Drawing Date	22/05/24					

WTT®

用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 1 or 1
--------------	-------------	------------------