


版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



- SPECIFICATIONS
- Current Rating: 3A AC, DC
 - Voltage Rating: 250V AC, DC
 - Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
 - Contact Resistance: $20\text{m}\Omega$ Max
 - Insulation Resistance: $1000\text{M}\Omega$ Min
 - Withstanding Voltang: 800V AC/minute
 - Material: Phosphoric bronze Tin-plated
 - Applicable Wire Sizes: AWG#22~28#

GENERAL TOLERANCE		制 图 Mapping	黄彬 2022、09、07		料 号 PART NO.		版 本 REV.	A
X.±0.25	X.'±2'		审 核 Audit	张伟 2022、09、07		品 名 TITLE	HX-PA2.0-T	页 次 SHEET
.X±0.20	.X'±1'	核 准 Approved		罗小春 2022、09、08		客户料号 CUTM. NO.		
.XX±0.15	.XX'±0.5'		单 位 Units	MM	比 例 SCALE	1:1	 韩下 HANXIA 深圳市韩下电子有限公司	
.XXX±0.10	.XXX'±0.5'							



深圳市韩下电子有限公司
Shenzhen Hanxia Electronic Co.,Ltd
Tel:0755-23086569

承 认 书

SPECIFICATION FOR APPROVAL

产 品 编 码
Material code:

产品名称 Project:

金属端子

规格型号 Part No:

HX-PA2.0-T

贵公司承认印 Approval signatures

料 号/Part No.	签 章/Signatures

日期 Date:

拟制/Drawn	黄彬	
审核/Check	张伟	
批准/Approved	罗小春	