












PCB LAYOUT (TOP VIEW)



(ø3.50mm 4 POLE PLUG DETAIL DRAWING)



3D VIEW



SCHEMATIC

NOTE:

1.ELECTRICAL CHARACTERISTICS:

1.1 RATINGS:DC 30V 0.5A

1.2 CONTACT RESISTANCE:100mΩ MAX

1.3 INSULATION RESISTANCE:100MΩ MIN

1.4 WITHSTAND VOLTAGE:AC 500V /1 Minute

1.5 WORKING TEMPERATURE:-25~+ 85°C

1.6 SOLDER HEAT RESISTANCE:245±5°C

2.MECHANICAL CHARACTERISTICS:

2.1 OPERATING FORCE:3~30N

2.2 SERVICE LIFE:5,000 Cycle.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: PJ-342 无头沉板全插 反功能	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW-PJ342D-100B
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2609221035
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1