









REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED




RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05

- 备注:
- 1.材质:
 - 1.1胶芯: LCP+30%G.F UL94V-0
 - 1.2端子: 高导铜7025: 镍底50U" MIN
接触区域镀金 (AU 1u")焊接区域镀金G/F
 - 1.3外壳: SUS304, T=0.30mm: 表面镀镍50U" MIN
 - 1.4中夹片: SUS301:
 - 2.主要特性:
 - 2.1额定电流: 5A
 - 2.2接触阻抗: 40mΩ MAX (初始值)
50mΩ MAX (测试后)
 - 2.3绝缘阻抗: 100MΩ MIN
 - 2.4耐压测试: 100V AC R M S
 - 2.5整体插入力:5-20N 整体插入力: 5-20N (耐久后)
整体拔出力: 8-20N 整体拔出力: 6-20N (耐久后)
 - 2.6耐久: 10000次
 - 2.7耐高温: SMT回流焊 (峰值260°±5°), 塑胶不能有起泡,
融胶等不良, 变色, 翘曲变形在公差范围以内。
 - 2.8产品须做焊锡测试, 粘锡面积达到95%以上:
 - 2.9盐雾测试: 24H MIN
 - 3.0工作温度: -25°C ~ +80°C



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME


料号编码:



Part Number		Product Description				
WTT-03F16BV950CG13		TYPE-C 16PIN on-board four-pin extended version L=9.5MM Shell without spring				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.35 X.X ± 0.25 X.XX ± 0.15 X.XXX ± 0.10	Units: Metric (mm)  3rd Angle Projection			
CHECKED	Xiong fangyuan					
APPROVED	Huangshaohuang					
Drawing Date	22/05/24					

WTT®
用心连接世界


SCALE 1:1 SIZE: A4 SHEET: 1 or 2




包 装 信 息	
每盘产品数	900pcs
每箱卷盘数	10卷
每箱产品数	9000pcs
产品单重	依实际填写
每箱净重	依实际填写
每箱毛重	依实际填写

- 备注:
1. 自动机包装前先剪掉2格后调整前段空出10格, 中间装900PCS产品, 尾端也需空出10格;
 2. 按照图示方向将成品一一放入REEL包装盘内, 依同一方向放入;
 3. 一个REEL包装盘放置900个成品, 装满成品的REEL盘外圈需装上保护带, 四周贴上美纹胶, 盘面贴一张内标签;
 4. 将每盘产品依次放入箱内, 一箱装10盘(900*10=9000PCS). 四周用三角板固定, 最后用透明胶纸将纸箱四周封实, 箱外贴上外标签;
 5. 若有未装满之零数箱, 必须以缓行材料塞满, 数量比较少时可单盘包装出货;

REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED



品名	规格	单位	用量
TYPE C 16PIN板上加长SMT	载带W=24mm PH=16mm T=0.40mm PET 透明	SET	1/900
上封带	自粘式透明上封带T0.05mm W20.7mm	m	13.5/900
三角板	K=K, 10CM*10CM*13CM, H32CM	PCS	4/9000
外箱	K=K, 外径35*35*33.5CM	PCS	1/9000

Part Number		Product Description				
WTT-03F16BV950CG13		TYPE-C 16PIN on-board four-pin extended version L=9.5MM Shell without spring				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.35 X.X ± 0.25 X.XX ± 0.15 X.XXX ± 0.10	Units: Metric (mm)			
CHECKED	Xiong fangyuan					
APPROVED	Huangshaohuang		 3rd Angle Projection			
Drawing Date	22/05/24					

WTT®
用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 2 or 2
--------------	-------------	------------------