










TABLE:



A180203111016 A180203111015 MD半成 MD半成 MD半成	环氧树脂	PK13001		
	外壳	S1846A500	SUS304R-1/2H.T=0.20mm	Ni:50u"Min;
	内壳	S1846A003	SUS304R-1/2H.T=0.30mm	Ni:50u"Min;
	护套	H18020301500	PA9T(G.F30%).BLACK.	/
	中夹片	S18428002		
P/N	端子	T18118010	C2680R-H.T=0.20mm	Ni:30u"Min; Au:CONTACT AREA:1u" Solder AREA:G/F
	塑胶	SY11034001	LCP(G.F30%) BLACK.	/
P/N	PART NAME	P/N	MATERIALS	FINISH




Recommended P.C.B. Layout
Unspecified tolerance:±0.05
(Top view)

NOTES:

1. CURRENT RATING:
3.0A MAX.
2. DIELECTRIC WITHSTAND VOLTAGE:
100VAC.
3. TEMPERATURE RANGE:
-30 °C ~ 85 °C.
4. CONTACT RESISTANCE:
40 MILLIONHM MAX.
5. INSULATION RESISTANCE:
100 MEGOHMS MIN.
6. INSERTION FORCE :
5N~20N.
7. UNMATING FORCE:
8N~20N.
8. DURABILITY:
10,000 CYCLES.
9. WATERPROOF RATING: IPX7.
10. ALL PRODUCTS COMPLY WITH RoHS
ENVIRONMENTAL REQUIREMENTS.



A5	CC1	B12	GND
A9	VBUS	B9	VBUS
		B5	CC2
		B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME









Part Number		Product Description				
WTT-22F06BV730FS03		Type-C 6PIN board with two foot plug-in board waterproof female seat adhesive type L=7.30MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.25 X.X ± 0.20 X.XX ± 0.15 X.XXX ± 0.10	Units: Metric (mm)			
CHECKED	Xiong fangyuan					
APPROVED	Huangshaohuang		 3rd Angle Projection			
Drawing Date	22/05/24					

WTT®

用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 1 or 2
--------------	-------------	------------------

REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED
A1		修改外壳和塑胶护套形状, 改善外壳扣不紧	2025.10.29	LEN.SONG		



- 说明:
- 1, 将检查合格的产品, 放入承载带中, 一盘包装600PCS;
 - 2, 将11盘承载带放入纸箱中;
 - 3, 将纸箱封装好, 贴上标签.

每箱数量	净重 (Kg)	毛重 (Kg)
6000PCS	xxx	xxx

Part Number		Product Description			
WTT-22F06BV730FS03		Type-C 6PIN board with two foot plug-in board waterproof female seat adhesive type L=7.30MM			
CUSTOMER DRAWING					
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.25 X.X ± 0.20 X.XX ± 0.15 X.XXX ± 0.10	Units: Metric (mm)	 COMPLIANT ©2012 UL LLC UL94V-0	
CHECKED	Xiong fangyuan				
APPROVED	Huangshaohuang		 3rd Angle Projection		 RoHS COMPLIANT 2011/05/EU Deca-BDE
Drawing Date	22/05/24				

WTT®

用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 2 or 2
--------------	-------------	------------------