











RECOMMENDED P. C. B. LAYOUT
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$

料号编码:



REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVE

备注:

1.材质:

1.1 胶芯: LCP+30%G.F UL94V-0

1.2 端子: 高导铜C7025, T=0.15mm

1.3 外壳: SUS304, T=0.30mm

1.4 中夹片: SUS301, $T=0.15\text{mm}$

2.主要特性:

2.1 额定电流: 5A

2.2接触阻抗: 40mΩ MAX(初始值)
50mΩ MAX(测试后)

2.3绝缘阻抗: 100M Ω E MIN

2.4耐压测试: 100V AC R.M.S

2.6整体插入力: 5-20N 整体插入力: 5-20N (耐久后)

整体拔出力:8-20N 整体拔出力:6-20N (耐久后)



2.7耐久：10000次

2.8耐高温：SMT回流焊（峰值 $260^{\circ}\pm 5^{\circ}$ ），塑胶不能有起泡，融胶等不良，变色，翘曲变形在公差范围以内；

2.9产品须做焊锡测试,粘锡面积达到95%以上

3.0盐雾测试: 48H MIN

3.1 工作温度: $-30^{\circ}\text{C} \sim +85^{\circ}\text{C}$



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

Part Number		Product Description					WTT® 用心连接世界		
WTT-04F16AV680CG24		TYPE-C 16PIN Vertical SMD H6.8MM							
CUSTOMER DRAWING									
DRAWN	Zhang Xincheng	Tolerances (Except as Noted): GENERAL TOLERANCE: X. ± 0.40 X.X ± 0.30 X.XX ± 0.20 X XXX ± 0.10	Units:				SCALE 1:1	SIZE: A4	SHEET: 1 or 2
CHECKED	Xiong fangyuan		Metric (mm)						
APPROVED	Huangshaohuang								
Drawing Date	22/05/24		3rd Angle Projection						

