







3D VIEW



SCHEMATIC

P.C.B LAYOUT
TOP VIEW

(ø3.50mm 4 POLE PLUG DETAIL DRAWING)

NOTE:

1.ELECTRICAL CHARACTERISTICS:

1.1 RATINGS:DC 30V 0.5A

1.2 CONTACT RESISTANCE:100mΩ MAX

1.3 INSULATION RESISTANCE:100MΩ MIN

1.4 WITHSTAND VOLTAGE:AC 500V /1 Minute

1.5 WORKING TEMPERATURE:-25~+

1.6 SOLDER HEAT RESISTANCE:245±5°C

2.MECHANICAL CHARACTERISTICS:

2.1 OPERATING FORCE:3~30N

2.2 SERVICE LIFE:5,000 Cycle.

	HOUSING	1 PCS	HIGH TEMPERATURE PLASTIC	BLACK COLOR
06	CONTACT F	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
05	CONTACT E	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
04	CONTACT D	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
03	CONTACT C	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
02	CONTACT B	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
01	CONTACT A	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
ITEM	PART NAME	Q'TY	MATERIAL	DESCRIPTION



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5' UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: PJ-342 沉板 无头全贴	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW02-PJ342C-130B
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2609220916
			SHEET NO.	1 OF 1