












RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)
(FOR REFERENCE ONLY)



METAL MASK T=0.10
TOLERANCE±0.05(钢网推荐图)
(FOR REFERENCE ONLY)



NOTES:

1:MATERIAL:

1-1:STAINLESS STEEL THICKNE=0.08mm

2:FINISH:

2-1:SEE DETAILED LIST.

3:PRODUCT SPECIFICATIONS:

3-1:RATED CURRENT:1.0A/MAX

3-2:VOLTAGE RATING:1.50V/AC/DC/MAX

3-3:CONTACT RESISTANCE:80mΩ/MAX

3-4:OPERATING TEMPERATURE:-40°C~85°C

3-5:NORMAL FORCE OF PRESS@3.10:0.40N MIN ON CONTACT POINT.

3-6:DURABILITY:1,500 CYCLES.

4:SALT SPRAY:SEE DETAILED LIST

5:PACKING SPECIFICATION:REEL&TARE

6:DIMENSIONS MARKED ◻,CPK>1.33


7:ALL DIMENSIONS MARKED ▼ MUST BE CONTROLLED BY QC;

8:COMPLIANT TO RoHS&LEAD FREE




深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: L3.50*W1.50*H1.40mm侧接弹片	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW-TXT351514AP
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2609171544
			SHEET NO.	1 OF 1





PULL OUT
IN THIS DIRECTION
引出方向



TOTAL
20LAYERS

PULL OUT
IN THIS DIRECTION/引出方向



⑤		ADHESIVE TAPE	
④		CARRIER TAPE	W12.0
③		TOP COVER	W7.50
②	1	LABLE	
①	1	ROLLER DISK	ø330
ITEM	QT'Y	NAME	SIZE



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图
UNIT: mm [inch] SCALE:1:1 SIZE: A4	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. MOLD NO.
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: SHEET NO. 1 OF 1