








SCHEMATIC



1. 电气及机械特性要求如下:
 - 1.1 接触阻抗: 50mΩ以下;
 - 1.2 绝缘阻抗: 100MΩ以上;
 - 1.3 耐电压: 500V AC以上;
 - 1.4 耐插拔: 5,000次以上;
 - 1.5 插入力: 0.3~3.0kgf (3~30N);
 - 1.6 拔出力: 0.3~3.0kgf (3~30N) .
2. 产品符合RoHS环保标准要求.



RECOMMENDED PCB LAYOUT
TOP VIEW TOL:±0.05




(ø3.50mm 4 POLE PLUG DETAIL DRAWING)

09	HOUSING	1 PCS	HIGH TEMPERATURE PLASTIC	BLACK COLOR
08	CONTACT G	1 PCS	BRASS T=0.20	Au Plated
07	CONTACT G	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
06	CONTACT F	1 PCS	BRASS T=0.20	Au Plated
05	CONTACT E	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
04	CONTACT D	1 PCS	BRASS T=0.20	Au Plated
03	CONTACT C	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
02	CONTACT B	1 PCS	BRASS T=0.20	Au Plated
01	CONTACT A	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
ITEM	PART NAME	Q'TY	MATERTAL	DESCRIPTION



深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: PJ-393C 8P 全插5.5头	
X.X ±0.30					
X.XX ±0.25					
X.XXX ±0.15					
X: ±2°	X.X: ±0.5°	CHECKED BY:	DATE :	PART NO.	HYCW-PJ393C8P-550B
		马跃	2014-02-23	MOLD NO.	
UNIT: mm [inch]		APPROVED BY:	DATE :	DRAW NO:	HYC-2609211446
SCALE:1:1	SIZE: A4	邱敏	2014-02-23	SHEET NO.	1 OF 1