






3D VIEW



SCHEMATIC

RIGHT PACKING P.C.B LAYOUT
TOP VIEW

(Ø3.50mm 4 POLE PLUG DETAIL DRAWING)

NOTE:

1.ELECTRICAL CHARACTERISTICS:

1.1 RATINGS:DC 30V 0.5A

1.2 CONTACT RESISTANCE:100mΩ MAX

1.3 INSULATION RESISTANCE:100MΩ MIN

1.4 WITHSTAND VOLTAGE:AC 500V /1 Minute

1.5 WORKING TEMPERATURE:-25~+ 85°C

1.6 SOLDER HEAT RESISTANCE:245±5°C

2.MECHANICAL CHARACTERISTICS:

2.1 OPERATING FORCE:3~30N

2.2 SERVICE LIFE:5,000 Cycle.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: PJ-342 无头沉板 五插一贴反功能	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-PJ342G-100B	MOLD NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2609221041	SHEET NO. 1 OF 1