




3D VIEW







推荐选5#;6#端为检测PIN

SCHEMATIC

NOTES:

1. CONTACT CURRENT RATING:1A;
2. CONTACT RESISTANCE:50mΩ MAX;
3. INSULATION RESISTANCE:100MΩ MIN;
4. DIELECTRIC WITHSTANDING:500V AC MIN;
5. DURABILITY:5000CYCLES MIN;
6. CONNECTOR MATING FORCES:2.94~29.4N(0.3~3.0kgf);
7. CONNECTOR UNMATING FORCES:2.94~29.4N(0.3~3.0kgf);

06	CONTACT F	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
05	CONTACT E	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
04	CONTACT D	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
03	CONTACT C	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
02	CONTACT B	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
01	CONTACT A	1 PCS	STAINLESS STEEL, T=0.20	Au Plated
07	HOUSING	1 PCS	HIGH TEMPERATURE PLASTIC	BLACK,
ITEM	PART NAME	Q'TY	MATERIAL	DESCRIPTION

RIGHT PACKING P.C.B LAYOUT
TOP VIEW

2.50mm 4 POLE PLUG DETAIL DRAWING)



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5" UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: PJ-242	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW02-PJ242-120B
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2609210903
			SHEET NO.	1 OF 1