



公司品牌 WTT - XX X X X XXX XX XX 产品流水号

内部编码

产品类型
M:公座系列
F:母座系列

PIN 数
06:6P
16:16P
24:24P
以此类推

产品系列
CG:常规系列
FS:防水系列
DT:外壳带弹片系列
WZ:无定位柱系列

产品长度
650:6.5H
680:6.8H
740:7.4H
8.8:8.8H
以此类推

上板类型
S:全贴
D:插件
J:夹板
V:插贴
H:焊线

产品结构
A:立式
B:卧式
C:侧立式

Part Number		Product Description				
WTT-22F04AD150FS02		USB AF2.0 Direct Plug H15.0MM Waterproof Female Socket				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.40 X.X ± 0.35 X.XX ± 0.25 X.XXX ± 0.20	Units: Metric (mm)	 COMPLIANT 2017 UL LLC UL94V-0	 RoHS COMPLIANT 2011/05/EU Deca-BDE	 REACH COMPLIANT 2019/07/26 SVHC
CHECKED	Xiong fangyuan		 3rd Angle Projection			
APPROVED	Huangshaohuang					
Drawing Date	22/05/24					

WTT®

用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 1 or 1
--------------	-------------	------------------

NETOS:

一.电气特性:Electrical:

- 1.额定电流: Current Rating : 1.5A/contact terminal.
- 2.额定电压: Voltage Rating: 30V DC.
- 3.接触阻抗:Contact Resistance: 30 milliohms MAX.
- 4.耐电压:Dielectnic Withstanding Voitage: 100 V AC AT Sea Levol.
- 5.绝缘阻抗:lnsulation Resistance: 1000 MΩ Mlin.

二.物理性能:Mechanical:

- 1.插拔力: Cnnector Mate and Unmate Force: Mate force:3.57kgf(MAX). Unmate force:1.02kgf(MIN) .


三.原材料:Material:

- 1.塑胶:Housing: HIGH-TEMPERATURE PLASTIC. BLACK. UL 94 V-0.
- 2.端子: COPPER ALLOY. T0.25mm.
- 3.外壳: STAINLESS STEEL.T0.30mm.
- 4.护套: HIGH-TEMPERATURE PLASTIC. BLACK,UL94V-0.
- 5.防水圈: 硅胶 60D. 黑色.
- 6.防尘塞: HIGH-TEMPERATURE PLASTIC. BLACK. UL 94 V-0.

四.电镀:Finish:

- 1.端子: PIATED GOLD IN MATING AREA. TIN ON SOLDER TALLS. BOTTOM PLATING NICKEL.
- 2.外壳: NICKEL PLATING.

五. 盐雾: 24H.



PIN ASSIGNMENT:

PIN NO.	1	2	3	4
SINGAL NAME	VBUS	D-	D+	GND