


推荐选5#;6#端为检测PIN

NOTES:

1. CONTACT CURRENT RATING:1A;
2. CONTACT RESISTANCE:50mA MAX;
3. INSULATION RESISTANCE:100MΩ MIN;
4. DIELECTRIC WITHSTANDING:500V AC MIN;
5. DURABILITY:5000CYCLES MIN;
6. CONNECTOR MATING FORCES:(0.3~3.0kgf);
7. CONNECTOR UNMATING FORCES:(0.3~3.0kgf);

06	CONTACT F	1 PCS	PHOSPHOR BRONZE, T=0.25	Au Plated
05	CONTACT E	1 PCS	PHOSPHOR BRONZE, T=0.25	Au Plated
04	CONTACT D	1 PCS	PHOSPHOR BRONZE, T=0.25	Au Plated
03	CONTACT C	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
02	CONTACT B	1 PCS	PHOSPHOR BRONZE, T=0.25	Au Plated
01	CONTACT A	1 PCS	PHOSPHOR BRONZE, T=0.25	Au Plated
07	HOUSING	1 PCS	HIGH TEMPERATURE PLASTIC	BLACK
ITEM	PART NAME	Q'TY	MATERIAL	DESCRIPTION



深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME:	
X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'				PJ-342 有头双柱 前两插后四贴	
 UNIT: mm [inch]		CHECKED BY:	DATE :	PART NO.	HYCW-PJ342BJ-140B
		马跃	2014-02-23	MOLD NO.	
SCALE: 1:1 SIZE: A4		APPROVED BY:	DATE :	DRAW NO:	HYC-2609221123
		邱敏	2014-02-23	SHEET NO.	1 OF 1