





推荐选5#;6#端为检测PIN
SCHEMATIC



NOTES:

1. CONTACT CURRENT RATING:1A;
2. CONTACT RESISTANCE:50mA MAX;
3. INSULATION RESISTANCE:100MΩ MIN;
4. DIELECTRIC WITHSTANDING:500V AC MIN;
5. DURABILITY:5000CYCLES MIN;
6. CONNECTOR MATING FORCES:(0.3~3.0kgf);
7. CONNECTOR UNMATING FORCES:(0.3~3.0kgf);



(ø3.50mm 3 OR 4 POLE PLUG DETAIL DRAWING)

06	CONTACT F	1 PCS	PHOSPHOR BRONZE, T=0.25	Au Plated
05	CONTACT E	1 PCS	PHOSPHOR BRONZE, T=0.25	Au Plated
04	CONTACT D	1 PCS	PHOSPHOR BRONZE, T=0.25	Au Plated
03	CONTACT C	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
02	CONTACT B	1 PCS	PHOSPHOR BRONZE, T=0.25	Au Plated
01	CONTACT A	1 PCS	PHOSPHOR BRONZE, T=0.25	Au Plated
07	HOUSING	1 PCS	HIGH TEMPERATURE PLASTIC	BLACK
ITEM	PART NAME	Q'TY	MATERIAL	DESCRIPTION



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2° X.X* ±0.5°	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: PJ-342 有头双柱 全贴
CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. MOLD NO.	HYCW02-PJ342B-140B
APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO. SHEET NO.	HYC-2609221101 1 OF 1

RIGHT PACKING P.C.B LAYOUT
TOP VIEW