






RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



5PIN 以上加逃料



SPECIFICATIONS

1. Current rating: 2A AC, DC
2. Temperature range: -25°C ~ +85°C
3. Insulation resistance: 100MΩ Min.
4. Withstanding voltage: 500V AC/ minute.
5. Contact resistance: 20mΩ Max.

Material:

Insulator: PA4T UL 94V-0
Contact: Phosphor Bronze or Brass
Plating: Plated Tin or Plated Gold
Circuits: 02~15P
Mate with:XFCN P1201 series Housing

Ordering Code:

M1201RS-xx-BK
1 2

- 1.序列号
- 2.Pin位数 02-20P

No.of PIN/ROW	Dimension		
	A	B	C
2	1.20	2.60	4.20
3	2.40	3.80	5.40
4	3.60	5.00	6.60
5	4.80	6.20	7.80
6	6.00	7.40	9.00
7	7.20	8.60	10.20
8	8.40	9.80	11.40
9	9.60	11.00	12.60
10	10.80	12.20	13.80
11	12.00	13.40	15.00
12	13.20	14.60	16.20
13	14.40	15.80	17.40
14	15.60	17.00	18.60
15	16.80	18.20	19.80

X.±0.50	X.°±	PART NO: M1201RS-xx-BK	XFCN 兴飞连接器				
.X±0.25	.X°±						
.XX±0.15	.XX°±						
.XXX±0.10	.XXX°±						
UNITS:	mm	TITLE: 1.20mm Crimp Style Connectors	0769-82001899				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN			www.xfconn.com				
			DWG NO:				
			/				
		APPD	Chen ZhiQiang				
		CHKD	Liu Wei		VIEW		
		DRAW	Chen HongJiang		SCALE	SHEET	REV
		DATE	2024.07.24		NONE	1/1	A1