








General Specification
Current Rating:1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating:125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20℃~+70℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance:≤30mΩ
Insulation Resistance:≥500MΩ
Dielectric Strength:500V AC/(50HZ)/Min
Mating And Unmating Force:3~20N
Durability:750 Cycles Min

Material Specification
Housing :Thermo-plastic, UL94V-0.
Contact :Alloy Copper
Shield :Alloy Copper
Please refer to the customer drawing when customer has specified



3	插 针	PHOSPHOR BRONZE	32	FU ^o	
2	后 盖	PA46	4	BLACK	
1	塑 座	PA46	1	BLACK	
序号	名 称	材 料	数 量	镀层/颜色	备 注



网络插座外形图

绘 图:	吴 飞	日 期:	2022.4.8
审 核:	王 德	日 期:	
核 准:	李 生	日 期:	

一 般 公 差		品 名:	RCH-52-42-14(全塑无灯)			
30~	±0.25	料 号:	WR01137			
10~30	±0.20	型 号:	RJ45		图 号:	
~10	±0.15					
角 度:	±2°	版 本:				
页 面:	1 of 1	单 位:mm	比 例: 1:1	纸 张: A4		

改 造 电 气 上 面 图 在 止 禁

A/0 新出版发行

版次 变 更 履 历

变更单号 绘 制 日 期

该 图 面 供 温 州 瑞 川 电 子 有 限 公 司 内 部 使 用 , 不 得 私 自 复 印