

1

2

3

4

5

A

A

B

B

C



C

D

D

E




E



GT-PG025 A-F 02-H025 N

G-SWITCH

Product No

Female
F=FemaleNumber Of Pins
02=2PinHigh Product(mm)
H025=2.5Detail
N=Without magnetism**G-Switch Specification:**

- 1.Rated load: 2A
- 2.Rated voltage:DC/AC 12V
- 3.Contact resistance: 100mΩ max
- 4.Durability cycle: 10,000 Cycles Min
- 5.Operating temperature range: -40°C ~ +85°C
- 6.Salt spray: 48 Hours

1	PIN	COPPER ALLOY C3602	Au3u" PLATED
2	BASE	PA9T+30%GF	BLACK
NO.	PART NAME	MATERIAL	REMARK

SCALE: 1:1
UNIT: mm
SIZE: A4Unless otherwise
General tolerance:
X ±0.30
X.x ±0.20
X.xx ±0.10
X* ±3°Title: Horizontal Pogopin Female 2Pin Pitch2.54
DIP 5.1×2.8×H2.5 mm

Molde Code: GT-PG025A-F02-H025N

DRAWN	CHECKED	APPROVED	DATE
Xla	Chen	Chen	2026.04.27

品贊科技
b-Switch
www.dg-switch.com

REV: A0 SHEET: 1/1