







PART NO	PIN	A	B
WAFER-JC1.5-2PJK	2	1.5	4.0
WAFER-JC1.5-3PJK	3	3.0	5.5
WAFER-JC1.5-4PJK	4	4.5	7.0
WAFER-JC1.5-5PJK	5	6.0	8.5
WAFER-JC1.5-6PJK	6	7.5	10.0
WAFER-JC1.5-7PJK	7	9.0	11.5
WAFER-JC1.5-8PJK	8	10.5	13.0
WAFER-JC1.5-9PJK	9	12.0	14.5
WAFER-JC1.5-10PJK	10	13.5	16.0
WAFER-JC1.5-11PJK	11	15.0	17.5
WAFER-JC1.5-12PJK	12	16.5	19.0
WAFER-JC1.5-13PJK	13	18.0	20.5
WAFER-JC1.5-14PJK	14	19.5	22.0
WAFER-JC1.5-15PJK	15	21.0	23.5
WAFER-JC1.5-16PJK	16	22.5	25.0
WAFER-JC1.5-17PJK	17	24.0	26.5
WAFER-JC1.5-18PJK	18	25.5	28.0
WAFER-JC1.5-19PJK	19	27.0	29.5
WAFER-JC1.5-20PJK	20	28.5	31.0

技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):50V AC,DC.
- 3.耐电压(Withstanding Voltage):500V AC/minute.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.额定电流(Rated Current): 0.7A AC,DC.

材料:

- 1.塑胶:PA66 白色



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: JC15 WTB弯插板胶壳	
DECIMALS:	ANGLES:	PAR	WAFER-JC1.5-NPJK
X.: ± 0.50	$\pm 1^{\circ}$	DWN	Lucas
X.X: ± 0.20		CHKD	Ethan
X.XX: ± 0.10		APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A