









REV.	ECN NO OR DESCRIPTION	REVISED	DATE



技术指标:

- 1.塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
- 2.温度范围: -40°C~85°C.
- 3.额定电压: 50V, AC.
- 4.接触电阻: ≤0.02Ω.
- 5.绝缘电阻: ≥100MΩ

序号	品名	材质
①	0.5 Pitch双槽立式BTB公座嵌芯	PA10T UL94 V-0 颜色:黑色
②	0.5 Pitch双槽立式BTB公座端子	铜合金/表面点镀金
③	0.5 Pitch双槽立式BTB公座吸盘	LCP UL94 V-0颜色:黑色.



High photosynthesis (H)	合高	The female seat neight 母座单高 (H1)	The male seat neight 公座单高 (H2)	Insertion height (H3)
3.00		2.20	0.80	1.60
3.50		2.20	1.30	1.60
4.00		3.00	1.00	1.90
4.50		3.50	1.00	1.90
5.00		4.00	1.00	1.90
5.50		4.50	1.00	1.90
6.00		4.00	2.00	1.90
6.50		4.50	2.00	1.90
7.00		3.00	4.00	1.90
7.50		3.50	4.00	1.90
8.00		4.00	4.00	1.90
8.50		4.50	4.00	1.90

UNLESS OTHERWISE SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10

TITLE	0.5 Pitch双槽立式BTB公(单高4.0)			
DWN	xiong	PART NO.	BTM0540-XXPSLYR-GO	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY



PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
BTM0540-8PSLYR-GO	8	1.50	2.50	4.70	3.40	4.00
BTM0540-10PSLYR-GO	10	2.00	3.00	5.20	3.90	
BTM0540-12PSLYR-GO	12	2.50	3.50	5.70	4.40	
BTM0540-14PSLYR-GO	14	3.00	4.00	6.20	4.90	
BTM0540-16PSLYR-GO	16	3.50	4.50	6.70	5.40	
BTM0540-18PSLYR-GO	18	4.00	5.00	7.20	5.90	
BTM0540-20PSLYR-GO	20	4.50	5.50	7.70	6.40	
BTM0540-22PSLYR-GO	22	5.00	6.00	8.20	6.90	
BTM0540-24PSLYR-GO	24	5.50	6.50	8.70	7.40	
BTM0540-26PSLYR-GO	26	6.00	7.00	9.20	7.90	
BTM0540-28PSLYR-GO	28	6.50	7.50	9.70	8.40	
BTM0540-30PSLYR-GO	30	7.00	8.00	10.20	8.90	
BTM0540-32PSLYR-GO	32	7.50	8.50	10.70	9.40	8.00
BTM0540-34PSLYR-GO	34	8.00	9.00	11.20	9.90	
BTM0540-36PSLYR-GO	36	8.50	9.50	11.70	10.40	
BTM0540-38PSLYR-GO	38	9.00	10.00	12.20	10.90	
BTM0540-40PSLYR-GO	40	9.50	10.50	12.70	11.40	
BTM0540-44PSLYR-GO	44	10.50	11.50	13.70	12.40	
BTM0540-50PSLYR-GO	50	12.00	13.00	15.20	13.90	
BTM0540-60PSLYR-GO	60	14.50	15.50	17.70	16.40	
BTM0540-70PSLYR-GO	70	17.00	18.00	20.20	18.90	
BTM0540-80PSLYR-GO	80	19.50	20.50	22.70	21.40	
BTM0540-100PSLYR-GO	100	24.50	25.50	27.70	26.40	

REV.	ECN NO OR DESCRIPTION	REVISED	DATE

UNLESS OTHERWISE SPECIFED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS: ANGLES:		TITLE	0.5 Pitch双槽立式BTB公(单高4.0)			
X :±0.30	X :±2°	DWN	xiong	PART NO. BTM0540-XXPSLYR-O		
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
		CUSTOMER COPY				