








REV.	ECN NO OR DESCRIPTION				REVISED	DATE
		合高(H)			公座单高	母座单高
		3.0			2.2	2.2
		3.5			2.2	2.7
		4.0			2.2	3.2
		5.0			2.6	4.4
CKT	A	B	C	D		
2X4	1.50	2.60	4.10	3.60		
2X5	2.00	3.10	4.60	4.10		
2X6	2.50	3.60	5.10	4.60		
2X7	3.00	4.10	5.60	5.10		
2X8	3.50	4.60	6.10	5.60		
2X9	4.00	5.10	6.60	6.10		
2X10	4.50	5.60	7.10	6.60		
2X11	5.00	6.10	7.60	7.10		
2X12	5.50	6.60	8.10	7.60		
2X13	6.00	7.10	8.60	8.10		
2X14	6.50	7.60	9.10	8.60		
2X15	7.00	8.10	9.60	9.10		
2X16	7.50	8.60	10.10	9.60		
2X17	8.00	9.10	10.60	10.10		
2X18	8.50	9.60	11.10	10.60		
2X19	9.00	10.10	11.60	11.10		
2X20	9.50	10.60	12.10	11.60		
2X22	10.50	11.60	13.10	12.60		
2X25	12.00	13.10	14.60	14.10		
2X30	14.50	15.60	17.10	16.60		
2X35	17.00	18.10	19.60	19.10		
2X40	19.50	20.60	22.10	21.60		

		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
TITLE		0.5 Pitch B型单槽立式BTB公座业务(单高2.6)无焊片镀金			
DWN	xiong	PART NO.BTM0526-XXPDLYR-GO			
CHKD	lee	SCALE:1:1	UNIT: mm		
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4	
CUSTOMER COPY					

- 技术指标:
- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
 - 温度范围: -40°C~85°C.
 - 额定电压: 125V, AC.
 - 接触电阻: ≤0.02Ω.
 - 绝缘电阻: ≥100MΩ

序号	品名	材质
①	0.5 Pitch B型单槽立式BTB公座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型单槽立式BTB公座端子	铜合金/表面点镀金



 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
TITLE0.5 PitchB型单槽立式BTB公座业务(单高2.6)无焊片镀金				
DWN	xiong	PART NO.BTM0526-XXPDLYR-GO		
CHKD	lee	SCALE:1:1	UNIT:mm	
APVD	wang	SIZE:A4	SHEET:10F 1	REV:A4
CUSTOMER COPY				