

SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP 30% G/F UL 94V-0

1.2 COLOR:BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

1.4 PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:





2.1 CONTACT:1u" GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDERTAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG:100u" TIN PLATING ON SOLDERTAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL



RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE: ± 0.05



ITEM	DIM A	形状	DIM E
SATA-021FB-22PS1BY	2.10		2.08
SATA-021F-22PS1BY	2.30		

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:		ANGLES:	
X	: ± 0.30	X	: $\pm 2^\circ$
X.X	: ± 0.20	X.X	: $\pm 1^\circ$
X.XX	: ± 0.10		



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	SATA 7+15P 母座板下6.74SMT侧插鱼叉			
DWN	xiong	PART NO. SATA-021F-22PS1BY		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4

CUSTOMER COPY