









REV.	ECN NO OR DESCRIPTION	REVISED	DATE



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100M\Omega$

High photosynthesis 合高 (H)	The female seat neight 母座单高 (H1)	The male seat neight 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90



序号	品名	材质
①	0.5 Pitch双槽立式 BTB公座胶芯	PA10T UL94 V-0 颜色:黑色
②	0.5 Pitch双槽立式 BTB公座端子	铜合金/表面点镀金
③	0.5 Pitch双槽立式 BTB公座吸盖	LCP UL94 V-0颜色:黑色.

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:	ANGLES:
X :±0.30	X :±2°
X.X :±0.20	X.X :±1°
X.XX :±0.10	



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	0.5 Pitch双槽立式BTB公(单高1.0)			
DWN	xiong	PART NO.	BTM0510-XXPSLYR-GO	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
BTM0510-8PSLYR-GO	8	1.50	2.50	4.70	3.40	4.00
BTM0510-10PSLYR-GO	10	2.00	3.00	5.20	3.90	
BTM0510-12PSLYR-GO	12	2.50	3.50	5.70	4.40	
BTM0510-14PSLYR-GO	14	3.00	4.00	6.20	4.90	
BTM0510-16PSLYR-GO	16	3.50	4.50	6.70	5.40	
BTM0510-18PSLYR-GO	18	4.00	5.00	7.20	5.90	
BTM0510-20PSLYR-GO	20	4.50	5.50	7.70	6.40	
BTM0510-22PSLYR-GO	22	5.00	6.00	8.20	6.90	
BTM0510-24PSLYR-GO	24	5.50	6.50	8.70	7.40	
BTM0510-26PSLYR-GO	26	6.00	7.00	9.20	7.90	
BTM0510-28PSLYR-GO	28	6.50	7.50	9.70	8.40	8.00
BTM0510-30PSLYR-GO	30	7.00	8.00	10.20	8.90	
BTM0510-32PSLYR-GO	32	7.50	8.50	10.70	9.40	
BTM0510-34PSLYR-GO	34	8.00	9.00	11.20	9.90	
BTM0510-36PSLYR-GO	36	8.50	9.50	11.70	10.40	
BTM0510-38PSLYR-GO	38	9.00	10.00	12.20	10.90	
BTM0510-40PSLYR-GO	40	9.50	10.50	12.70	11.40	
BTM0510-44PSLYR-GO	44	10.50	11.50	13.70	12.40	
BTM0510-50PSLYR-GO	50	12.00	13.00	15.20	13.90	
BTM0510-60PSLYR-GO	60	14.50	15.50	17.70	16.40	
BTM0510-70PSLYR-GO	70	17.00	18.00	20.20	18.90	
BTM0510-80PSLYR-GO	80	19.50	20.50	22.70	21.40	
BTM0510-100PSLYR-GO	100	24.50	25.50	27.70	26.40	

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10

东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
TITLE	0.5 Pitch 双槽立式 BTB 公 (单高 1.0)			
DWN	xiong	PART NO. BTM0510-XXPSLYR-GO		
CHKD	lee	SCALE: 1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET: 1 OF 1	REV: A4
CUSTOMER COPY				