









技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

序号	品名	材质
①	0.8 Pitch F型 单槽立式BTB母座胶芯	PA9T UL94 V-0,颜色:黑色
②	0.8 Pitch F型 单槽立式母座端子	铜合金/表面点镀金
③	0.8 Pitch B型 单槽立式BTB麦拉	耐高温不干胶
总高(H)		公座单高(H1)
4.00		2.80
4.50		3.30
5.00		3.80
5.50		4.30
6.00		4.80
6.50		5.30
7.00		5.80

Part No	CKT	A	B	C	D
BTF0829-6PDLYR-GO	2*3	4.30	2.80	1.60	3.40
BTF0829-8PDLYR-GO	2*4	5.10	3.60	2.40	4.20
BTF0829-10PDLYR-GO	2*5	5.90	4.40	3.20	5.00
BTF0829-12PDLYR-GO	2*6	6.70	5.20	4.00	5.80
BTF0829-14PDLYR-GO	2*7	7.50	6.00	4.80	6.60
BTF0829-16PDLYR-GO	2*8	8.30	6.80	5.60	7.40
BTF0829-18PDLYR-GO	2*9	9.10	7.60	6.40	8.20
BTF0829-20PDLYR-GO	2*10	9.90	8.40	7.20	9.00
BTF0829-30PDLYR-GO	2*15	13.90	12.40	11.20	13.00
BTF0829-40PDLYR-GO	2*20	17.90	16.40	15.20	17.00
BTF0829-50PDLYR-GO	2*25	21.90	20.40	19.20	21.00
BTF0829-60PDLYR-GO	2*30	25.90	24.40	23.20	25.00
BTF0829-70PDLYR-GO	2*35	29.90	28.40	27.20	29.00
BTF0829-80PDLYR-GO	2*40	33.90	32.40	31.20	33.00
BTF0829-90PDLYR-GO	2*45	37.90	36.40	35.20	37.00
BTF0829-100PDLYR-GO	2*50	41.90	40.40	39.20	41.00

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:		0.8 Pitch F型单槽立式BTB母座业务图(单高2.9)			
ANGLES:		DWN xiong PART NO. BTF0829-XXPDLYR-GO			
X : ± 0.30		CHKD lee SCALE: 1:1 UNIT: mm			
X.X : ± 0.20		APVD wang SIZE: A4 SHEET: 1 OF 1 REV: A4			
X.XX : ± 0.10		CUSTOMER COPY			