










技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

REV.	ECN NO OR DESCRIPTION	REVISED	DATE
序号	品名	材质	
①	0.8 Pitch E型 单槽侧插BTB公座底座	LCP UL94 V-0, 颜色: 本色	
②	0.8 Pitch E型 单槽侧插BTB公座端子	铜合金/表面镀金	

Part No	CKT	A	B	C	D
BTM0835-4PDLYR-GO	2*2	0.80	2.35	3.35	2.60
BTM0835-6PDLYR-GO	2*3	1.60	3.15	4.15	3.40
BTM0835-8PDLYR-GO	2*4	2.40	3.95	4.95	4.20
BTM0835-10PDLYR-GO	2*5	3.20	4.75	5.75	5.00
BTM0835-12PDLYR-GO	2*6	4.00	5.55	6.55	5.80
BTM0835-14PDLYR-GO	2*7	4.80	6.35	7.35	6.60
BTM0835-16PDLYR-GO	2*8	5.60	7.15	8.15	7.40
BTM0835-18PDLYR-GO	2*9	6.40	7.95	8.95	8.20
BTM0835-20PDLYR-GO	2*10	7.20	8.75	9.75	9.00
BTM0835-22PDLYR-GO	2*11	8.00	9.55	10.55	9.80
BTM0835-24PDLYR-GO	2*12	8.80	10.35	11.35	10.60
BTM0835-26PDLYR-GO	2*13	9.60	11.15	12.15	11.40
BTM0835-28PDLYR-GO	2*14	10.40	11.95	12.95	12.20
BTM0835-30PDLYR-GO	2*15	11.20	12.75	13.75	13.00
BTM0835-32PDLYR-GO	2*16	12.00	13.55	14.55	13.80
BTM0835-34PDLYR-GO	2*17	12.80	14.35	15.35	14.60
BTM0835-36PDLYR-GO	2*18	13.60	15.15	16.15	15.40
BTM0835-38PDLYR-GO	2*19	14.40	15.95	16.95	16.20
BTM0835-40PDLYR-GO	2*20	15.20	16.75	17.75	17.00
.....	...	...	...	...	...
BTM0835-80PDLYR-GO	2*40	31.20	32.75	33.75	33.00

UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10

TITLE	0.8 Pitch E型单槽侧插BTB公座底座(单高3.5)			
DWN	xiong	PART NO. BTM0835-XXPDLYR-GO		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY