



SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP UL 94V-0

1.2 COLOR:BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

1.4 PEG:C2680R-H,T=0.50mm

2.FINISH:










2.1 CONTACT: 1u"/3u"/5u"/15u" GOLDPLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDERTAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG: 100u" TIN PLATING ON SOLDERTAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL



环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS: ANGLES:		TITLE: SATA 7+15P 母座 DIP 180°双排双鱼叉加长型 针长2.70		
X	:±0.30	X	:±2°	DWN xiong PART NO. SATA-032F-22PS1BY
X.X	:±0.20	X.X	:±1°	CHKD lee SCALE:1:1 UNIT: mm
X.XX	:±0.10	APVD wang	SIZE: A4	SHEET:10F 1 REV: A4
CUSTOMER COPY				