








REV.	ECN NO OR DESCRIPTION	REVISED	DATE



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.03\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$

序号	品名	材质
①	0.5 Pitch D型单槽侧插 BTB母座胶芯	LCP UL94 V-0,颜色:本色
②	0.5 Pitch D型单槽侧插 BTB母座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
BTF0553-4PDLYR-GO	2*2	0.50	2.54	3.50	2.20
BTF0553-6PDLYR-GO	2*3	1.00	3.04	4.00	2.70
BTF0553-8PDLYR-GO	2*4	1.50	3.54	4.50	3.20
BTF0553-10PDLYR-GO	2*5	2.00	4.04	5.00	3.70
BTF0553-12PDLYR-GO	2*6	2.50	4.54	5.50	4.20
BTF0553-14PDLYR-GO	2*7	3.00	5.04	6.00	4.70
BTF0553-16PDLYR-GO	2*8	3.50	5.54	6.50	5.20
BTF0553-18PDLYR-GO	2*9	4.00	6.04	7.00	5.70
BTF0553-20PDLYR-GO	2*10	4.50	6.54	7.50	6.20
BTF0553-22PDLYR-GO	2*11	5.00	7.04	8.00	6.70
BTF0553-22PDLYR-GO	2*12	5.50	7.54	8.50	7.20
BTF0553-26PDLYR-GO	2*13	6.00	8.04	9.00	7.70
BTF0553-28PDLYR-GO	2*14	6.50	8.54	9.50	8.20
BTF0553-30PDLYR-GO	2*15	7.00	9.04	10.00	8.70
BTF0553-32PDLYR-GO	2*16	7.50	9.54	10.50	9.20
BTF0553-34PDLYR-GO	2*17	8.00	10.04	11.00	9.70
BTF0553-36PDLYR-GO	2*18	8.50	10.54	11.50	10.20
BTF0553-38PDLYR-GO	2*19	9.00	11.04	12.00	10.70
BTF0553-40PDLYR-GO	2*20	9.50	11.54	12.50	11.20
.....	...	...	...	...	...
BTF0553-80PDLYR-GO	2*40	19.50	21.54	22.50	21.20

UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS: ANGLES:

X : ± 0.30 X : $\pm 2^{\circ}$
X.X : ± 0.20 X.X : $\pm 1^{\circ}$
X.XX : ± 0.10

TITLE	0.5 Pitch D型单槽侧插BTB母座业务图(单高5.3)			
DWN	xiong	PART NO. BTF0553-XXPDLYR-GO		
CHKD	lee	SCALE: 1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET: 10F 1	REV: A4

CUSTOMER COPY