



SPECIFICATION:

1.MATERIAL:







- 1.1 HOUSING: LCP 30% G/F UL 94V-0
- 1.2 COLOR: BLACK
- 1.3 CONTACT: BRASS C2680R-H, T=0.25mm
- 1.4 PEG: BRASS C2680R-H, T=0.30mm

2.FINISH:

- 2.1 CONTACT: 1u", 3u", 5u", 15u" GOLD PLATING ON CONTACT AREA
- 2.2 100u" MIN. TIN PLATING ON SOLDER TAILS
- 2.3 40u" MIN. NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:

- 3.1 CURRENT RATING: 1.5 AMPERE PER CONTACT
 - 3.2 CONTACT RESISTANCE: 30 MILLIOHMS MAX
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHMS MIN
 - 3.4 DIELECTRIC WITH STANDING VOLTAGE: 500 VDC
 - 3.5 OPERATING TEMPERATURE: -40°C ~ +85°C
4. THE MARK (X) DIMENSIONS MUST BE MEASURED BY FAI.



环境要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS:		TITLE		
X : ±0.30		SATA7+15P 公座沉板式SMT H0.9 (半包式) 缺口接地片		
X.X : ±0.20		DWN	xiong	PART NO. SATA-034M-22PS1BY
X.XX : ±0.10		CHKD	lee	SCALE: 1:1 UNIT: mm
		APVD	wang	SIZE: A4 SHEET: 10F 1 REV: A4
CUSTOMER COPY				