








REV.	ECN NO OR DESCRIPTION	REVISED	DATE



Part No	CKT	A	B	C
BTFO8117-20PDLYR-GO	2*10	7.20	13.80	12.20
BTFO8117-22PDLYR-GO	2*11	8.00	14.60	13.00
BTFO8117-24PDLYR-GO	2*12	8.80	15.40	13.80
BTFO8117-26PDLYR-GO	2*13	9.60	16.20	14.60
BTFO8117-28PDLYR-GO	2*14	10.40	17.00	15.40
BTFO8117-30PDLYR-GO	2*15	11.20	17.80	16.20
BTFO8117-32PDLYR-GO	2*16	12.00	18.60	17.00
BTFO8117-34PDLYR-GO	2*17	12.80	19.40	17.80
BTFO8117-36PDLYR-GO	2*18	13.60	20.20	18.60
BTFO8117-38PDLYR-GO	2*19	14.40	21.00	19.40
BTFO8117-40PDLYR-GO	2*20	15.20	21.80	20.20
BTFO8117-42PDLYR-GO	2*21	16.00	22.60	21.00
BTFO8117-44PDLYR-GO	2*22	16.80	23.40	21.80
BTFO8117-46PDLYR-GO	2*23	17.60	24.20	22.60
BTFO8117-48PDLYR-GO	2*24	18.40	25.00	23.40
BTFO8117-50PDLYR-GO	2*25	19.20	25.80	24.20
.....	...	...	...	...
BTFO8117-200PDLYR-GO	2*100	79.20	85.80	84.20

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C。
3. 额定电压: 100V, AC。
4. 接触电阻: ≤0.05Ω。
5. 绝缘电阻: ≥500MΩ

序号	品名	材质
①	0.8 Pitch B型立式 BTB插座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.8 Pitch B型立式 BTB插座端子	铜合金/表面点镀金
③	0.8 Pitch B型立式 BTB插座吸盘	不锈钢

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	0.8 Pitch B型立式BTB插座业务图(单高11.7)			
DWN	xiong	PART NO.BTFO8117-XXPDLYR-GO		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4
CUSTOMER COPY				



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

公座 (PLUG) 母座 (SOCKET)				

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	0.8 Pitch B型立式BTB插座系列(间距11.7)			
DWN	xiong	PART NO	BTFO8117-XXPDLYR-GO	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4

CUSTOMER COPY