








REV.	ECN NO OR DESCRIPTION	REVISED	DATE



Part No	CKT	A	B	C
BTM0867-20PDLYR-GO	2*10	7.20	13.80	12.20
BTM0867-22PDLYR-GO	2*11	8.00	14.60	13.00
BTM0867-24PDLYR-GO	2*12	8.80	15.40	13.80
BTM0867-26PDLYR-GO	2*13	9.60	16.20	14.60
BTM0867-28PDLYR-GO	2*14	10.40	17.00	15.40
BTM0867-30PDLYR-GO	2*15	11.20	17.80	16.20
BTM0867-32PDLYR-GO	2*16	12.00	18.60	17.00
BTM0867-34PDLYR-GO	2*17	12.80	19.40	17.80
BTM0867-36PDLYR-GO	2*18	13.60	20.20	18.60
BTM0867-38PDLYR-GO	2*19	14.40	21.00	19.40
BTM0867-40PDLYR-GO	2*20	15.20	21.80	20.20
BTM0867-42PDLYR-GO	2*21	16.00	22.60	21.00
BTM0867-44PDLYR-GO	2*22	16.80	23.40	21.80
BTM0867-46PDLYR-GO	2*23	17.60	24.20	22.60
BTM0867-48PDLYR-GO	2*24	18.40	25.00	23.40
BTM0867-50PDLYR-GO	2*25	19.20	25.80	24.20
.....	...	...	...	...
BTM0867-200PDLYR-GO	2*100	79.20	85.80	84.20

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 100V, AC.
4. 接触电阻: ≤0.05Ω.
5. 绝缘电阻: ≥500MΩ

序号	品名	材质
①	0.8 Pitch B型立式 BTB公座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.8 Pitch B型立式 BTB公座端子	铜合金/表面点镀金
③	0.8 Pitch B型立式 BTB公座吸盖	不锈钢

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	0.8 Pitch B型立式BTB公座业务图(单高6.7)			
DWN	xiong	PART NO.	BTM0867-XXPDLYR-GO	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4
CUSTOMER COPY				



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

公座 (PLUG) 母座 (SOCKET)				

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	0.8 Pitch B型BTBA系列(间距6.7)			
DWN	xiong	PART NO.	BTM0867-XXPDLYR-GO	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY