




技术指标(Technical Index):

- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V DC/AC(rms).
- 3.额定电流(Rated current):2.0A AC,DC.
- 4.耐压值(Dielectricwithstanding voltage):1000V AC/minute.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.适用线规(Apply to gauge):AWG#24~#28.
- 7.适用基板厚度(Applicable PC board thickness):1.2~1.6mm.



序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: JC20 WTB弯插板端子
DECIMALS:	ANGLES:		PAR WAFER-JC2.0-DZ
X.:±0.50	±1°		DWN Lucas
X.X:±0.20			CHKD Ethan
X.XX:±0.10			APVD Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A