







SECTION A-A



PCB LAYOUT



SECTION B-B



SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP/PA9T COLOR:BLACK

1.2 CONTACT:BRASS C2680R-H,T=0.25mm

1.3 PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

2.1 CONTACT: 1u"/3u"/5u"/5u" GOLD PLATING ON CONTACT AREA

2.2 100u" MIN. TIN PLATING ON SOLDERTAILS

2.3 30u" MIN.NICKEL UNDERPLATING OVER ALL

2.4 PEG: 100u" MIN. TIN PLATING ON SOLDERTAILS

2.5 30u" MIN.NICKEL UNDERPLATING OVER ALL

环境要求		产品必须符合ROHS要求						
3	Peg	Brass C2680		Tin/Ni Plated				
2	Terminal	Brass C2680		Gold/Tin Plated				
1	Housing	High Temp	Black	UL 94V-0				
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK				
UNLESS OTHERWISE SPECIFIED TOLERANCES			东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD					
DECIMALS: ANGLES:			TITLE SATA 7P 公座B型 全开开窗 鱼叉式 (鱼叉式中心距12.83)					
X	:±0.30	X	:±2°	DWN	xiong	PART NO.	SATA-015M-07PS1BY	
X.X	:±0.20	X.X	:±1°	CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX	:±0.10			APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY								