





PART NO	PIN	A	B
WAFER-JC2.0-2PJK	2	2.00	4.5
WAFER-JC2.0-3PJK	3	4.00	6.5
WAFER-JC2.0-4PJK	4	6.00	8.5
WAFER-JC2.0-5PJK	5	8.00	10.5
WAFER-JC2.0-6PJK	6	10.00	12.5
WAFER-JC2.0-7PJK	7	12.00	14.5
WAFER-JC2.0-8PJK	8	14.00	16.5
WAFER-JC2.0-9PJK	9	16.00	18.5
WAFER-JC2.0-10PJK	10	18.00	20.5
WAFER-JC2.0-11PJK	11	20.00	22.5
WAFER-JC2.0-12PJK	12	22.00	24.5
WAFER-JC2.0-13PJK	13	24.00	26.5
WAFER-JC2.0-14PJK	14	26.00	28.5
WAFER-JC2.0-15PJK	15	28.00	30.5
WAFER-JC2.0-16PJK	16	30.00	32.5
WAFER-JC2.0-17PJK	17	32.00	34.5
WAFER-JC2.0-18PJK	18	34.00	36.5
WAFER-JC2.0-19PJK	19	36.00	38.5
WAFER-JC2.0-20PJK	20	38.00	40.5

技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V AC,DC.
- 3.耐电压(Withstanding Voltage):1000V AC/minute.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.额定电流(Rated Current): 2A AC,DC.

材料:

- 1.塑胶:PA66 白色



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: JC20 WTB弯插板胶壳	
DECIMALS:	ANGLES:	PAR	WAFER-JC2.0-NPJK
X.: ± 0.50	$\pm 1^{\circ}$	DWN	Lucas
X.X: ± 0.20		CHKD	Ethan
X.XX: ± 0.10		APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A