






SCHEMATIC

NOTES :

1.0) RATING :


- 1.1. VOLTAGE : 12 VDC (R.M.S.)
- 1.2. CURRENT : 1 AMPERE MAXIMUM PER CONTACT AT 30° T-RISE
- 1.3. TEMPERATURE : -25° TO +85°

2.0) ELECTRICAL CHARACTERISTIC


- 2.1. CONTACT RESISTANCE : INITIAL 50m MAX. AFTER 100m
- 2.2. INSULATION RESISTANCE : 100 M MIN.
- 2.3. DIELECTIC WITHSTANDING VOLTAGE : 500 VAC AT SEA LEVEL

3.0) MECHANICAL :

- 3.1. DURABILITY ,MINIMUM: MATED 5000 CYCLES WITHOUT DEGRADING ELECTRICAL
- 3.2. INITIAL:MATING FORCE: 300g~2000g.UNMATING FORCE: 200g~2000g
- 3.3. AFTER LIFE TESTING:MATING FORCE: 300g~2000g.UNMATING FORCE: 200g~2000g



RECOMMEND PAD LAYOUT



MALE PLUG SCHEMATIC



深圳市华宇创精密电子有限公司

|                                                                            |                    |                      |                             |                   |
|----------------------------------------------------------------------------|--------------------|----------------------|-----------------------------|-------------------|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br>X.' ±2" X.X' ±0.5" | DRAWN BY :<br>陈一鸣  | DATE :<br>2014-02-23 | PART NAME:<br>3.5耳机座 斜口两插四贴 |                   |
|                                                                            | CHECKED BY:<br>马跃  | DATE :<br>2014-02-23 | PART NO.                    | HYCW-PJ06F65-470B |
| UNIT: mm [inch]<br>SCALE:1:1 SIZE: A4                                      | APPROVED BY:<br>邱敏 | DATE :<br>2014-02-23 | DRAW NO:                    | HYC-2609281615    |
|                                                                            |                    |                      | SHEET NO.                   | 1 OF 1            |