








| REV. | ECN NO OR DESCRIPTION | REVISED | DATE |
|------|-----------------------|---------|------|
|      |                       |         |      |
|      |                       |         |      |



| Part No             | CKT   | A     | B     | C     |
|---------------------|-------|-------|-------|-------|
| BTF0877-20PDLYR-GO  | 2*10  | 7.20  | 13.80 | 12.20 |
| BTF0877-22PDLYR-GO  | 2*11  | 8.00  | 14.60 | 13.00 |
| BTF0877-24PDLYR-GO  | 2*12  | 8.80  | 15.40 | 13.80 |
| BTF0877-26PDLYR-GO  | 2*13  | 9.60  | 16.20 | 14.60 |
| BTF0877-28PDLYR-GO  | 2*14  | 10.40 | 17.00 | 15.40 |
| BTF0877-30PDLYR-GO  | 2*15  | 11.20 | 17.80 | 16.20 |
| BTF0877-32PDLYR-GO  | 2*16  | 12.00 | 18.60 | 17.00 |
| BTF0877-34PDLYR-GO  | 2*17  | 12.80 | 19.40 | 17.80 |
| BTF0877-36PDLYR-GO  | 2*18  | 13.60 | 20.20 | 18.60 |
| BTF0877-38PDLYR-GO  | 2*19  | 14.40 | 21.00 | 19.40 |
| BTF0877-40PDLYR-GO  | 2*20  | 15.20 | 21.80 | 20.20 |
| BTF0877-42PDLYR-GO  | 2*21  | 16.00 | 22.60 | 21.00 |
| BTF0877-44PDLYR-GO  | 2*22  | 16.80 | 23.40 | 21.80 |
| BTF0877-46PDLYR-GO  | 2*23  | 17.60 | 24.20 | 22.60 |
| BTF0877-48PDLYR-GO  | 2*24  | 18.40 | 25.00 | 23.40 |
| BTF0877-50PDLYR-GO  | 2*25  | 19.20 | 25.80 | 24.20 |
| .....               | ...   | ...   | ...   | ...   |
| BTF0877-200PDLYR-GO | 2*100 | 79.20 | 85.80 | 84.20 |

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围:  $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ .
3. 额定电压: 100V, AC.
4. 接触电阻:  $\leq 0.05\Omega$ .
5. 绝缘电阻:  $\geq 500\text{M}\Omega$

| 序号 | 品名                     | 材质                   |
|----|------------------------|----------------------|
| ①  | 0.8 Pitch B型立式 BTB插座胶芯 | LCP UL94 V-0, 颜色: 本色 |
| ②  | 0.8 Pitch B型立式 BTB插座端子 | 铜合金/表面点镀金            |
| ③  | 0.8 Pitch B型立式 BTB插座吸盘 | 不锈钢                  |

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:  
X :±0.30 X :±2°  
X.X :±0.20 X.X :±1°  
X.XX :±0.10



东莞市汉博电子科技有限公司  
DONGGUAN HANBO TECHNOLOGY CO., LTD

| TITLE | 0.8 Pitch B型立式BTB插座业务图(单高7.7) |                             |             |         |
|-------|-------------------------------|-----------------------------|-------------|---------|
| DWN   | xiong                         | PART NO. BTF0877-XXPDLYR-GO |             |         |
| CHKD  | lee                           | SCALE:1:1                   | UNIT: mm    |         |
| APVD  | wang                          | SIZE: A4                    | SHEET:10F 1 | REV: A4 |

CUSTOMER COPY



| REV. | ECN NO OR DESCRIPTION | REVISED | DATE |
|------|-----------------------|---------|------|
|      |                       |         |      |
|      |                       |         |      |

|   |                                                     |  |  |  |  |
|---|-----------------------------------------------------|--|--|--|--|
| A | <div>公座<br/>(PLUG)</div> <div>母座<br/>(SOCKET)</div> |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
| B |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
| C |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
| D |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |
|   |                                                     |  |  |  |  |

UNLESS OTHERWISE  
SPECIFIED TOLERANCES

DECIMALS: ANGLES:  
X :±0.30 X :±2°  
X.X :±0.20 X.X :±1°  
X.XX :±0.10



东莞市汉博电子科技有限公司  
DONGGUAN HANBO TECHNOLOGY CO., LTD

|       |                               |           |                    |         |
|-------|-------------------------------|-----------|--------------------|---------|
| TITLE | 0.8 Pitch B型立式BTB母座业务图(单高7.7) |           |                    |         |
| DWN   | xiong                         | PART NO.  | BTf0877-XXPDLYR-G0 |         |
| CHKD  | lee                           | SCALE:1:1 | UNIT: mm           |         |
| APVD  | wang                          | SIZE: A4  | SHEET:10F 1        | REV: A4 |

CUSTOMER COPY