











PIN NO.	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F	DIM G
4P	4.18	1.50	2.57	3.38	3.10	3.90	2.50
5P	4.68	2.00	3.07	3.88	3.60	4.40	3.00
6P	5.18	2.50	3.57	4.38	4.10	4.90	3.50
7P	5.68	3.00	4.07	4.88	4.60	5.40	4.00
8P	6.18	3.50	4.57	5.38	5.10	5.90	4.50
9P	6.68	4.00	5.07	5.88	5.60	6.40	5.00
10P	7.18	4.50	5.57	6.38	6.10	6.90	5.50
11P	7.68	5.00	6.07	6.88	6.60	7.40	6.00
12P	8.18	5.50	6.57	7.38	7.10	7.90	6.50
13P	8.68	6.00	7.07	7.88	7.60	8.40	7.00
14P	9.18	6.50	7.57	8.38	8.10	8.90	7.50
15P	9.68	7.00	8.07	8.88	8.60	9.40	8.00
16P	10.18	7.50	8.57	9.38	9.10	9.90	8.50
17P	10.68	8.00	9.07	9.88	9.60	10.40	9.00
18P	11.18	8.50	9.57	10.38	10.10	10.90	9.50
19P	11.68	9.00	10.07	10.88	10.60	11.40	10.00
20P	12.18	9.50	10.57	11.38	11.10	11.90	10.50
21P	12.68	10.00	11.07	11.88	11.60	12.40	11.00
22P	13.18	10.50	11.57	12.38	12.10	12.90	11.50
23P	13.68	11.00	12.07	12.88	12.60	13.40	12.00
24P	14.18	11.50	12.57	13.38	13.10	13.90	12.50
25P	14.68	12.00	13.07	13.88	13.60	14.40	13.00
26P	15.18	12.50	13.57	14.38	14.10	14.90	13.50
27P	15.68	13.00	14.07	14.88	14.60	15.40	14.00
28P	16.18	13.50	14.57	15.38	15.10	15.90	14.50
29P	16.68	14.00	15.07	15.88	15.60	16.40	15.00
30P	17.18	14.50	15.57	16.38	16.10	16.90	15.50

SPECIFICATIONS:

1.MATERIALS:

1.1Housing: Thermoplastic,High Temp. UL94V-0,Color: White.

1.2Actuator: Thermoplastic,High Temp. UL94V-0,Color: Black.

1.3.Contacts: Copper alloy.

1.4Fitting Nail: Copper alloy.

2.Finish:

2.1 Contact:

50-100u"Nickel Under plating Overall.

3u"Gold On Contact And Gold Flash On Solder.

2.2Fitting Nail:

100-200u"Tin Plating On Solder Tails (Lead Free) .

50-100u"Nickel Under plating Overall.

3.Electrical:

3.1Current Rating:0.5A DC

3.2Voltage Rating:50V AC

3.3Contact Resistance:60mΩ Max

3.4Dielectric Withstanding Voltage:200V AC for 1 minute

3.5Insulation Resistance: 500MΩ Min

4.Environment characteristics:

4.1Operating Temperature: -40℃~+85℃

Products meet RoHS environmental requirements



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X' ±2" X.X' ±0.5'

UNIT: mm [inch]

SCALE:1:1

SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

0.5PH 1.0H 前插后压FPC

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW6D-05FPCXX-100B

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2609231140

SHEET NO.

1 OF 1