

A

B

C

D

E




F

G

H



I

J



1.20±0.25

3.40±0.25



PART NO	PIN	A	B
WAFER-JC2.5-2PJK	2	2.50	5.5
WAFER-JC2.5-3PJK	3	5.00	8.0
WAFER-JC2.5-4PJK	4	7.50	10.5
WAFER-JC2.5-5PJK	5	10.00	13.0
WAFER-JC2.5-6PJK	6	12.50	15.5
WAFER-JC2.5-7PJK	7	15.00	18.0
WAFER-JC2.5-8PJK	8	17.50	20.5
WAFER-JC2.5-9PJK	9	20.00	23.0
WAFER-JC2.5-10PJK	10	22.50	25.5
WAFER-JC2.5-11PJK	11	25.00	28.0
WAFER-JC2.5-12PJK	12	27.50	30.5
WAFER-JC2.5-13PJK	13	30.00	33.0
WAFER-JC2.5-14PJK	14	32.50	35.5
WAFER-JC2.5-15PJK	15	35.00	38.0
WAFER-JC2.5-16PJK	16	37.50	40.5

技术指标(Technical Index):

- 1.温度范围(Temperature range):-25°C~+85°C.
- 2.额定电压(Rated voltage):250V AC,DC.
- 3.耐电压(Withstanding Voltage):1000V AC/minute.
- 4.接触电阻(Contact resistance):≤20mΩ.
- 5.绝缘电阻(Insulation resistance):≥1000MΩ.
- 6.额定电流(Rated Current): 2.5A AC,DC.

材料:

- 1.塑胶:PA66 白色

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: JC25 WTB弯插板胶芯	
			PAR	WAFER-JC2.5-NPJK
DECIMALS:	ANGLES:		DWN	Lucas
X.:±0.50	±1°		CHKD	Ethan
X.X:±0.20			APVD	Jacob
X.XX:±0.10		CUSTOMER COPY		SCALE:1:1
		SIZE:A4		UNIT:MM
		SHEET:1F1		REV:A