

SPECIFICATION:

1.MATERIAL:

1.1 HOUSING:LCP 30% G/F UL 94V-0

1.2 COLOR:BLACK

1.3 CONTACT:BRASS C2680R-H,T=0.25mm

2.FINISH:

2.1 CONTACT:1u",3u",5u",15u"30u"GOLD PLATING ON CONTACT AREA

2.2 100u" MIN.TIN PLATING ON SOLDERTAILS

2.3 40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:




3.1 CURRENT RATING:1.5 AMPERE PER CONTACT

3.2 CONTACT RESISTANCE:30 MILLIOHMS MAX

3.3 INSULATION RESISTANCE:1000 MEGOHMS MIN

3.4 DIELECTRIC WITH STANDING VOLTAGE:500 VDC

3.5 OPERATING TEMPERATURE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$



环境要求		产品必须符合ROHS要求			
2	Terminal	BRASS C2680R—H		Gold/Tin Plated	
1	Housing	High Temp	Black	UL 94V—0	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK	
UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS: ANGLES:			TITLE	SATA 7+15P 夹角公座夹板1.0七个孔	
X :±0.30	X :±2°		DWN	xiong	PART NO. SATA-026M-22PS1BY
X.X :±0.20	X.X :±1°		CHKD	lee	SCALE:1:1 UNIT: mm 
X.XX :±0.10			APVD	wang	SIZE: A4 SHEET:1OF 1 REV: A4
		CUSTOMER COPY			