








1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ 。
3. 额定电压: $50\text{V}, \text{AC}$ 。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 500\text{M}\Omega$



REV.	ECN NO OR DESCRIPTION			REVISED	DATE
序号	品名		材质		
①	0.8 Pitch F型 单槽立式BTB公座胶芯		PA9T UL94 V-0,颜色:黑色		
②	0.8 Pitch F型 单槽立式公座端子		铜合金/表面点镀金		
总高(H)		公座单高(H)		母座单高(H)	
		H	H1		
4.00		2.80	1.80	2.90	
4.50		3.30			
5.00		3.80			
5.50		4.30	2.30	3.40	
6.00		4.80			
6.50		5.30			
7.00				3.90	
	CKT	A	B	C	D
	2*3	4.30	2.80	1.60	3.40
	2*4	5.10	3.60	2.40	4.20
	2*5	5.90	4.40	3.20	5.00
	2*6	6.70	5.20	4.00	5.80
	2*7	7.50	6.00	4.80	6.60
	2*8	8.30	6.80	5.60	7.40
	2*9	9.10	7.60	6.40	8.20
	2*10	9.90	8.40	7.20	9.00
	2*15	13.90	12.40	11.20	13.00
	2*20	17.90	16.40	15.20	17.00
	2*25	21.90	20.40	19.20	21.00
	2*30	25.90	24.40	23.20	25.00
	2*35	29.90	28.40	27.20	29.00
	2*40	33.90	32.40	31.20	33.00
	2*45	37.90	36.40	35.20	37.00
	2*50	41.90	40.40	39.20	41.00
 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD					
TITLE		0.8 Pitch F型单槽立式BTB公座业务图(单高3.3)			
DWN	xiong	PART NO.BTM0833-XXPDLYR-GO			
CHKD	lee	SCALE:1:1	UNIT: mm		
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4	
CUSTOMER COPY					