







REV.		ECN NO OR DESCRIPTION		REVISED	DATE
		序号	品名	材质	
		①	0.5 Pitch B型 单槽立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色	
		②	0.5 Pitch B型 单槽立式BTB母座端子	铜合金/表面点镀金	
		③	0.5 Pitch B型 单槽立式BTB母座焊片	铜合金/表面镀锡	
	A	B	C	D	E
	2.00	3.20	4.70	6.06	4.10
	2.50	3.70	5.20	6.56	4.60
	3.00	4.20	5.70	7.06	5.10
	3.50	4.70	6.20	7.56	5.60
	4.00	5.20	6.70	8.06	6.10
0	4.50	5.70	7.20	8.56	6.60
1	5.00	6.20	7.70	9.06	7.10
2	5.50	6.70	8.20	9.56	7.60
3	6.00	7.20	8.70	10.06	8.10
4	6.50	7.70	9.20	10.56	8.60
5	7.00	8.20	9.70	11.06	9.10
6	7.50	8.70	10.20	11.56	9.60
7	8.00	9.20	10.70	12.06	10.10
8	8.50	9.70	11.20	12.56	10.60
9	9.00	10.20	11.70	13.06	11.10
0	9.50	10.70	12.20	13.56	11.60
2	10.50	11.70	13.20	14.56	12.60
5	12.00	13.20	14.70	16.06	14.10
0	14.50	15.70	17.20	18.56	16.60
5	17.00	18.20	19.70	21.06	19.10
0	19.50	20.70	22.20	23.56	21.60
 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD					
TITLE		0.5 Pitch B型单槽立式BTB母座业务图(单高4.4)			
DWN	xiong	PART NO.BTF0544-XXPDLYC-GO			
CHKD	lee	SCALE:1:1	UNIT: mm		
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4	
CUSTOMER COPY					



技术指标:

1. 塑件表面应光洁, 无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: -40°C~85°C.
3. 额定电压: 125V, AC.
4. 接触电阻: ≤0.02Ω.
5. 绝缘电阻: ≥100MΩ



合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

UNLESS OTHERWISE SPECIFIED TOLERANCES				东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS: ANGLES:		TITLE	0.5 Pitch B型单槽立式BTB母座业务图(单高4.4)			
X :±0.30 X :±2°		DWN xiong	PART NO.BTF0544-XXPDLYC-GO			
X.X :±0.20 X.X :±1°		CHKD lee	SCALE:1:1	UNIT: mm		
X.XX :±0.10		APVD wang	SIZE: A4	SHEET:10F 1	REV: A4	
CUSTOMER COPY						